





MALE END VIEW

FEMALE END VIEW




- 1 = WHITE
- 2 = BLACK
- 3 = GREEN
- 4 = RED
- 5 = ORANGE
- 6 = BLUE
- 7 = BROWN
- 8 = YELLOW
- 9 = VIOLET
- 10 = GRAY
- 11 = PINK
- 12 = TAN
- 13 = WHITE/BLACK
- 14 = WHITE/GREEN
- 15 = WHITE/RED
- 16 = WHITE/BLUE



SPECIFICATIONS

CONTACT CARRIER MATERIAL/COLOR	NYLON or PBT/GRAY
MOLDED HEAD MATERIAL/COLOR	TPU/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	3.0 A
RATED VOLTAGE [V]	300 V
OUTER JACKET MATERIAL/COLOR	PVC/BLUE
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	16x22 AWG
DRAIN/SHIELD	NONE
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)
PROTECTION CLASS	IEC IP67



SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us		
	MATERIAL  SEE SPECIFICATIONS		DRFT RDS	DATE 04/09/09	DESCRIPTION  CSNM CKNWM 16-16-*
			APVD	SCALE 1=1.3	
	FINISH  SEE SPECIFICATIONS		UNIT OF MEASUREMENT <b>MILLIMETER [ INCH ]</b>	IDENTIFICATION NO.	
E UPDATE CONDUCTOR COLOR	NF 09/07/17	61751	DO NOT SCALE THIS DRAWING		
REV DESCRIPTION	BY DATE	ECO NO.	FILE: 777009183	SHEET 1 OF 1	