

## PRODUCT SPECIFICATIONS

P102x-12x, P104x-10x

# P1000 Series Rack Power Distribution Units

## APPLICATION

P1000 Series Rack Power Distribution Units are the ideal solution for data centers, computer rooms, and other high-demand environments that require “always-on” power. P1000 Series PDUs are available for both vertical and horizontal applications.



## SPECIFICATION

Power Distribution Units shall be offered in both vertical 0RU and horizontal (rack-mount) styles. PDUs shall include resettable overload protection. PDUs shall be cULus listed. PDUs shall be manufactured using a cold-rolled steel enclosure with a corrosion-resistant finish. Units shall feature a hard-wired power input cord. PDUs shall include all necessary hardware for both standard and button mounting. PDUs shall include industrial-grade receptacles utilizing industrial-rated plastic material and metal conductors.

## FEATURES

- 18 AWG cold-rolled steel enclosures
- Overload protection with easy-to-reset circuit breakers
- 30 A units feature UL489 rated circuit breakers
- LED indicators for “Power On” and “Polarity/Ground OK”
- Grounding connection point on all models
- Available for Zero-U and rack-mount applications

## DESIGN CONSIDERATIONS

- Standard mounting and button mounting hardware included
- Hard-wired power input cord on all models
- Corrosion-resistant powder coat finish
- cULus Listed

## STANDARDS & REGULATIONS

- UL 60950-1

## MECHANICAL SPECIFICATIONS

Dimensions: See page 2


## WARRANTY INFORMATION

For Leviton product warranties, go to [leviton.com/ns/warranty](http://leviton.com/ns/warranty)


P102x-12x, P104x-10x

**PRODUCT SPECIFICATIONS**  
**P102x-12x, P104x-10x**

Note: Illustrations not to scale.




P1021-12S, 120 V



P1023-12L, 120 V

P1040-10S, 120 V



P102x-12x, P104x-10x

P1044-10L, 120 V

**TECHNICAL SPECIFICATIONS VERTICAL P1000 SERIES PDUS**

Part Number	Nominal Input Voltage	Max Rated Amp.	Max Regulatory "Derated" Amperage	Overload Protection	Input Cord		Outlets		Dimensions in (mm)		
					Length (ft)	Plug Type	Qty.	Type	Height	Width	Depth
P1040-10S	120 V	15A	12A	Yes	10	5-15P	16	5-15R	30 (762)	1.80 (45.7)	1.75 (45.7)
P1041-10S	120 V	20A	16A	Yes	10	5-20P	16	5-20R	30 (762)	1.80 (45.7)	1.75 (45.7)
P1042-10L	120 V	20A	16A	Yes	10	L5-20P	16	5-20R	30 (762)	1.80 (45.7)	1.75 (45.7)
P1043-10S	120 V	20A	16A	Yes	10	5-20P	24	5-20R	48 (1219.2)	1.80 (45.7)	1.75 (45.7)
P1044-10L	120 V	20A	16A	Yes	10	L5-20P	24	5-20R	48 (1219.2)	1.80 (45.7)	1.75 (45.7)
P1045-10L	120 V	30A	24A	Yes	10	L5-30P	24	5-20R	48 (1219.2)	1.80 (45.7)	1.75 (45.7)

**TECHNICAL SPECIFICATIONS HORIZONTAL P1000 SERIES PDUS**

Part Number	Nominal Input Voltage	Max Rated Amp.	Max Regulatory "Derated" Amperage	Overload Protection	Input Cord		Outlets		Dimensions in (mm)		
					Length (ft)	Plug Type	Qty.	Type	Height	Width	Depth
P1020-12S	120 V	15A	12A	Yes	12	5-15P	10	5-15R	1.75 (45.7)	17.5 (444.5)	4.50 (114.3)
P1021-12S	120 V	20A	16A	Yes	12	5-20P	10	5-20R	1.75 (45.7)	17.5 (444.5)	4.50 (114.3)
P1022-12L	120 V	20A	16A	Yes	12	L5-20P	10	5-20R	1.75 (45.7)	17.5 (444.5)	4.50 (114.3)
P1023-12L	120 V	30A	24A	Yes	12	L5-30P	16	5-20R	3.50 (88.9)	17.5 (444.5)	4.50 (114.3)

For further support information, visit [leviton.com/ns/support](http://leviton.com/ns/support)