






MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS																							
<p>(LONG)</p>  <p>1 = WHITE 2 = RED 3 = GREEN/YELLOW 4 = ORANGE 5 = BLACK</p> 		 <p>1 = WHITE 2 = RED 3 = GREEN/YELLOW 4 = ORANGE 5 = BLACK</p> 		<table><tr><td>CONTACT CARRIER MATERIAL</td><td>TPU</td></tr><tr><td>MOLDED HEAD MATERIAL/COLOR</td><td>TPU/YELLOW</td></tr><tr><td>CONTACT MATERIAL/PLATING</td><td>BRASS/GOLD</td></tr><tr><td>COUPLING NUT MATERIAL</td><td>BRASS/NICKEL</td></tr><tr><td>RATED CURRENT [A]</td><td>10.0 A</td></tr><tr><td>RATED VOLTAGE [V]</td><td>600 V</td></tr><tr><td>OUTER JACKET MATERIAL/COLOR</td><td>TPE/YELLOW</td></tr><tr><td>CONDUCTOR INSULATION MATERIAL</td><td>TPE</td></tr><tr><td>NUMBER OF CONDUCTORS [AWG]</td><td>5x16 AWG</td></tr><tr><td>TEMPERATURE RANGE</td><td>-40°C to +105°C (-40°F to +221°F)</td></tr><tr><td>PROTECTION CLASS</td><td>NEMA 1,3,4,6P,12 &amp; IECIP67, IP68,IP69,IP69K</td></tr></table>		CONTACT CARRIER MATERIAL	TPU	MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW	CONTACT MATERIAL/PLATING	BRASS/GOLD	COUPLING NUT MATERIAL	BRASS/NICKEL	RATED CURRENT [A]	10.0 A	RATED VOLTAGE [V]	600 V	OUTER JACKET MATERIAL/COLOR	TPE/YELLOW	CONDUCTOR INSULATION MATERIAL	TPE	NUMBER OF CONDUCTORS [AWG]	5x16 AWG	TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)	PROTECTION CLASS	NEMA 1,3,4,6P,12 & IECIP67, IP68,IP69,IP69K
CONTACT CARRIER MATERIAL	TPU																										
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW																										
CONTACT MATERIAL/PLATING	BRASS/GOLD																										
COUPLING NUT MATERIAL	BRASS/NICKEL																										
RATED CURRENT [A]	10.0 A																										
RATED VOLTAGE [V]	600 V																										
OUTER JACKET MATERIAL/COLOR	TPE/YELLOW																										
CONDUCTOR INSULATION MATERIAL	TPE																										
NUMBER OF CONDUCTORS [AWG]	5x16 AWG																										
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)																										
PROTECTION CLASS	NEMA 1,3,4,6P,12 & IECIP67, IP68,IP69,IP69K																										




CABLE LENGTH	TOLERANCE *
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE *
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm
* UNLESS OTHERWISE SPECIFIED	

NOTES:

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
2. "/S1587" DESIGNATES WELDLIFE CABLE.

SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:  1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.  2. "/S1587" DESIGNATES WELDLIFE CABLE.					RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.				3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us			
					1.											
					2.											
					3.											
					4.											
					MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DRFT		RDS		DATE 01/26/07		DESCRIPTION  RSM RKM 56-*M/S1587	
									APVD				SCALE 1=1.5			
					FINISH		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT  MILLIMETER [ INCH ]				IDENTIFICATION NO.		REV F	
F					UPDATE PROTECTION CLASS					CBM		04/13/21		76628		
REV					DESCRIPTION					BY		DATE		ECO NO.		