








MALE END VIEW	TYPICAL PANEL CUTOUT	TYPICAL BOARD LAYOUT	SPECIFICATIONS																			
		 <p>SCALE: 2=1</p>	<table border="1"> <tr><td>CONTACT CARRIER MATERIAL/COLOR</td><td>NYLON OR TPU/BLACK</td></tr> <tr><td>CONTACT MATERIAL/PLATING</td><td>BRASS/GOLD</td></tr> <tr><td>HOUSING/LOCKNUT MATERIAL/PLATING</td><td>BRASS/NICKEL</td></tr> <tr><td>RATED CURRENT [A]</td><td>2.0 A</td></tr> <tr><td>RATED VOLTAGE [V]</td><td>60 VAC/75 VDC</td></tr> <tr><td>CONDUCTORS</td><td>PCB PINS</td></tr> <tr><td>TEMPERATURE RATING</td><td>-30°C to +105°C (-22°F to +221°F)</td></tr> <tr><td>PROTECTION CLASS</td><td>MEETS NEMA 1,3,4,6P AND IEC IP68</td></tr> <tr><td>MAX. PANEL THICKNESS</td><td>3.0 [0.12]</td></tr> </table>	CONTACT CARRIER MATERIAL/COLOR	NYLON OR TPU/BLACK	CONTACT MATERIAL/PLATING	BRASS/GOLD	HOUSING/LOCKNUT MATERIAL/PLATING	BRASS/NICKEL	RATED CURRENT [A]	2.0 A	RATED VOLTAGE [V]	60 VAC/75 VDC	CONDUCTORS	PCB PINS	TEMPERATURE RATING	-30°C to +105°C (-22°F to +221°F)	PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68	MAX. PANEL THICKNESS	3.0 [0.12]	
CONTACT CARRIER MATERIAL/COLOR	NYLON OR TPU/BLACK																					
CONTACT MATERIAL/PLATING	BRASS/GOLD																					
HOUSING/LOCKNUT MATERIAL/PLATING	BRASS/NICKEL																					
RATED CURRENT [A]	2.0 A																					
RATED VOLTAGE [V]	60 VAC/75 VDC																					
CONDUCTORS	PCB PINS																					
TEMPERATURE RATING	-30°C to +105°C (-22°F to +221°F)																					
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68																					
MAX. PANEL THICKNESS	3.0 [0.12]																					



SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:  
1. PIN SUPPORT IS FOR SHIPPING ONLY.

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	<div style="text-align: right;">           3000 CAMPUS DRIVE            MINNEAPOLIS, MN 55441            1-800-544-7769            (763) 553-7300            (763) 553-0708 fax            turck.com         </div> <div style="text-align: center;"> <b>TURCK INC</b>  <i>High Technology Sensors and Automation Controls</i> </div>		
MATERIAL  SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT RWC APVD	DATE 12/20/06 SCALE 1=1.0	DESCRIPTION  FSFDK 8-PCB	
FINISH  SEE SPECIFICATIONS	CONTACT TURCK FOR MORE INFORMATION	UNIT OF MEASUREMENT <b>MILLIMETER [ INCH ]</b> DO NOT SCALE THIS DRAWING		IDENTIFICATION NO.  U2-09449	REV  C
C DRAWING PROCESSED AS PART OF ECO 33971	CBM 04/07/11 33971	FILE: U2-09449			
REV DESCRIPTION	BY DATE ECO NO.	SHEET 1 OF 1			