




MALE END VIEW



- 1 = WHITE/ORANGE
- 2 = ORANGE
- 3 = WHITE/GREEN
- 4 = GREEN
- 5 = WHITE/BROWN
- 6 = BROWN
- 7 = WHITE/BLUE
- 8 = BLUE

SPECIFICATIONS

HOUSING MATERIAL	PA UL94-V0
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL	DIE-CAST ZINC
RATED CURRENT [A]	0.5 A
RATED VOLTAGE [V]	48 V
WIRE SIZE	26-22 AWG (SOLID OR STRANDED)
CABLE GRIP RANGE	5-9.7mm
TEMPERATURE RATING	-25°C to +85°C (-13°F to +185°F)
PROTECTION CLASS	IEC IP65, IP67
TRANSMISSION PERFORMANCE	CAT 6A PER IEC/PAS 61076-2-109



SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

1. SUITABLE FOR 10 GBIT AS PER IEEE 802.3an

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us	
1.				DRFT	RDS	DATE	09/07/11
2.				APVD	A.A.	SCALE	1=.8
3.		UNIT OF MEASUREMENT				DESCRIPTION	
4.		MILLIMETERS				CMB SX 8181-0	
MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		CONTACT TURCK FOR MORE INFORMATION		IDENTIFICATION NO.	
SEE SPECIFICATIONS						U2-19270	
FINISH						REV	
SEE SPECIFICATIONS						C	
				DO NOT SCALE THIS DRAWING		FILE: U2-19270	
						SHEET 1 OF 1	

C	UPDATE WIRE SIZE DESIGNATION	RDS	12/12/18	67752
REV	DESCRIPTION	BY	DATE	ECO NO.