



CABLE LENGTH	TOLERANCE *
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE *
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm
* UNLESS OTHERWISE SPECIFIED	

SOURCE DRAWING - FOR REFERENCE ONLY

0-7mm		±0.5mm
8-29mm		±1.0mm
30-49mm		±2.0mm
50-69mm		±3.0mm
70-100mm		±4.0mm
OVER 100mm		±5.0mm
* UNLESS OTHERWISE SPECIFIED		

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us					
1.				TURCK							
2.											
3.											
4.											
MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DRFT		RDS	DATE	04/03/14	DESCRIPTION		
SEE SPECIFICATIONS				APVD		E.S.	SCALE	1 = 1.0	DB9M DB9F-0.3M		
FINISH		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT				IDENTIFICATION NO.		REV	
SEE SPECIFICATIONS				MILLIMETER [INCH]				U2-22920		A	
DO NOT SCALE THIS DRAWING						FILE: U2-22920				SHEET 1 OF 1	

A	DRAWING RELEASE			RDS	04/03/14	
REV	DESCRIPTION			BY	DATE	ECO NO.