




MALE END VIEW






PIN-OUT DIAGRAM




SPECIFICATIONS

CONTACT CARRIER MATERIAL/COLOR	TPU/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
HOUSING MATERIAL/PLATING	BRASS/NICKEL
NUMBER OF CONTACTS	6 x 0.025 IN SQ. POSTS
RATED CURRENT [A]	1.0 A
RATED VOLTAGE [V]	50 VAC/60 VDC
TEMPERATURE RANGE	-30°C to +80°C (-22°F to +176°F)
MAXIMUM PCB THICKNESS	1.6 MM [0.06 IN]
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67



M8X1-6G

O-RING



10.0 [0.394]

0.5 [0.020] SQUARE (TYP)

RELATED DOCUMENTS


1. 8-164-02 revP2

2.

3.

4.

3RD ANGLE PROJECTION



THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.

DRFT RDS

APVD GC

DATE 12/17/02

SCALE 4=1

UNIT OF MEASUREMENT

MILLIMETER [ INCH ]

DO NOT SCALE THIS DRAWING

3000 CAMPUS DRIVE  
MINNEAPOLIS, MN 55441  
1-800-544-7769  
(763) 553-7300  
(763) 553-0708 fax  
www.turck.us

TURCK

DESCRIPTION

WMFS 6F-PCB

IDENTIFICATION NO.

U0902-43

REV

H

H

ADD DIMENSION

NF

08/22/17

61922

REV

DESCRIPTION

BY

DATE

ECO NO.