



TMS-CT

TE Internal #: EL7665-000
Printable Tubing, Continuous, Military, 3:1 Shrink Ratio, White, 4.2 mm [.166 in] Recovered Inside, -55 – 135 °C [-67 – 275 °F], TMS-CT
[View on TE.com >](#)

Identification & Labeling > Printable Tubing > Continuous Tube, Military Grade TMS-CT



Printable Tubing Type: **Continuous**
Printable Tubing Grade: **Military**
Printable Tubing Shrink Ratio: **3:1**
Primary Product Color: **White**
Supplied Inner Diameter: **12.7 mm [.5 in]**

[All Continuous Tube, Military Grade TMS-CT \(30\)](#)

Features

Product Type Features

Printable Tubing Type	Continuous
Printable Tubing Grade	Military

Body Features

Printable Tubing Shrink Ratio	3:1
Primary Product Color	White

Dimensions

Supplied Inner Diameter	12.7 mm[.5 in]
Recovered Inside Diameter	4.2 mm[.166 in]
Compatible Cable Diameter Range	4.6 – 10.8 mm[.183 – .425 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
---------------------	--



Printer Technology	Thermal Transfer
Packaging Features	
Packaging Quantity	50

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




 TE Part # 1-2186500-1 T3212-PRINTER	 TE Part # 1-2186502-1 T3224-PRINTER	 TE Part # 1-2186503-1 T3224-SWARE-PRINTER	 TE Part # CP8122-000 T6112DS-PRINTER
---	---	---	--



Also in the Series | TMS-CT



Customers Also Bought





Documents

Product Drawings

TMS-CT-50M-1/2-OUT-9

English

Datasheets & Catalog Pages

Printable Continuous Tubing

English

TMS-CT, Continuous Military Grade Heat Shrink Identification Tube.

English

Product Specifications

Product Specification

English

IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX

English

Instruction Sheets

Instruction Sheet (non U.S.)

English