# FAS20-4S-4G-A



## **Integrated Design:**

- AS-interface<sup>®</sup> station •
- Four input and four outputs •

## **Applications:**

- For dry environments
- For use with four • 3-wire discrete sensors

## Features:


- PNP short-circuit protected inputs •
- Short-circuit protected outputs •
- Glass filled nylon with nickel • plated brass connectors

This module provides one connector with four PNP inputs and four PNP outputs each for connection to AS-interface°. The wiring is simple screw terminals to support multiple I/O configurations.


A short-circuit on any I/O point is indicated by a fault signal per the AS-i v3.0 specification. All inputs are

powered from the auxillary power supply.

#### **Dimensions:**



## **Terminal Wiring:**



$\bigcirc$	•	• V+
Ø	-0 0-	<b>I</b> 3
Ø	-0-0	<b>1</b> 2
$\square$	-0-0-	<b>I</b> 1
$\square$	$ \sim$ $ -$	lo
$\square$		<b>O</b> 3
$\square$		<b>O</b> <sub>2</sub>
$\square$		<b>O</b> <sub>1</sub>
Ø		<b>O</b> 0
Ø		• V-

All outputs are powered from the auxillary power.

The node address can be set using an AS-i handheld addressing tool or via software through the AS-i master.

This station supports extended address mode (1-31 A/B).



TURCK

## **Module Specifications:**

#### Electrical

Operating Voltage Internal Current Consumption	18-31 Volts (from AS-i Network) 30 mA ≤ 1 A (total)			
Auxiliary Power Consumption				
Input Circuits	(4) PNP 3-wire sensors or dry contacts			
Input Short-Circuit (I <sub>max</sub> )	700 mA (from auxiliary power)			
lout (max)	700 mA (shared by sensors)			
Input Signal State	Off < 2mA On = 3.0 – 3.4 mA			
Input Delay	2.5 ms			
Output Circuits				
Output Current	$\leq$ 1 A (from auxiliary power, shared with inputs and outputs)			
LED Indications				
Aux LED	Off = Off			
	Green = On			
AS-i Network LED	Off = Off Green = Ok			
	Red/Green = Fault			
Connections				
AS-interface <sup>®</sup>	5-pin screw terminals			
Auxillary Power	5-pin screw terminals			
	Screw terminal torque = 0.5 Nm max.			
Device Address				
Address Adjustment	1A – 31A / 1B – 31B (V3.0)			
Mechanical				
Material	Nylon			
Operating Temperature	-13° to +158°F (-25° to +70°C)			
Protection	IP20 Pollution degree 2 environment			

### Data and Parameter Bit:

I/O Data	D <sub>3</sub>	D <sub>2</sub>	D <sub>1</sub>	Do	IO Code 7 ID Code A ID2 Code 7
	O <sub>3</sub>	O <sub>2</sub>	O <sub>1</sub>	O <sub>0</sub>	
	I3	l <sub>2</sub>	l <sub>1</sub>	lo	
Parameter Group	P <sub>3</sub>	P <sub>2</sub>	P <sub>1</sub>	Po	
	Not Used	Not Used	OGS Enable	IGS Enable	

Current parameter P0 represents IGS and OGS simultaneously.

I/O faults are reported via the AS-i peripheral fault bit.