

TY27M-NDT

General Information

Extended Product Type:	TY27M-NDT
Product ID:	7TAG009660R0028
EAN:	5415022262148
Catalog Description:	14IN,50LB,NYLON,2-PC,DETECTION-TY
Long Description:	Detectable Cable Tie, Bright Blue Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 334.57mm (13.172 Inches), Width of 6.86mm (0.27 Inch), Thickness of 1.52mm (0.06 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Bulk Pack

Categories

Products » [Low Voltage Products and Systems](#) » [Installation Products](#) » [Wire Management and Connectivity](#) » [Cable Ties](#)

Ordering

EAN:	5415022262148
UPC:	786209936684
Country of Origin:	United States (US)
Selling Unit of Measure:	each

Dimensions

Product Net Width:	0.27 in 7 mm
Product Net Depth / Length:	13.4 in 340 mm

Container Information

Package Level 1 Units:	500 piece
Package Level 1 Width:	20 in 508 mm
Package Level 1 Height:	1 in 25 mm
Package Level 1 Depth / Length:	14 in 356 mm
Package Level 2 Units:	1000 piece
Package Level 2 Width:	9.5 in 241 mm
Package Level 2 Height:	5 in 127 mm
Package Level 2 Depth / Length:	15.25 in 387 mm

Additional Information

Brand / Label:	Ty-Rap
Color:	Blue
Effective Date:	20100111
Lock Type:	Stainless Steel Barb
Material:	Nylon/Polyamide 6.6
Product Name:	PLASTIC CABLE TIE
Product Type:	Detectable
Tensile Strength:	120 lb 540 N
Thickness:	

0.06 in
1.52 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	TY27M-NDT
Instructions and Manuals:	TY27M-NDT

Classifications

ETIM 6:	EC000046 - Cable tie
ETIM 7:	EC000046 - Cable tie
ETIM 8:	EC000046 - Cable tie
UNSPSC:	39121703
WEEE Category:	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC):	5034 >> Cable ties

