

TE Internal #: 2410400-2  
 Heat Shrink Equipment, Shuttle, Worldwide, Stub Splice / Cable  
 Assembly / Hose & Pipe Protection, Holding Tool, 220 V, 26 mm  
 Substrate Diameter

[View on TE.com >](#)



Application Tooling > Heat Shrink Equipment



Equipment Processing Type: **Shuttle**

Heat Shrink Equipment Region: **Worldwide**

Heat Shrink Equipment Application: **Battery, Cable Assembly, Hose & Pipe Protection, In-Line Splice, Ring Terminal, SolderSleeves, Stub Splice**

Tooling Type: **Holding Tool**

Operating Voltage: **220 V**

### Features

#### Electrical Characteristics

Operating Voltage	220 V
-------------------	-------

#### Dimensions

Tubing Outer Diameter (Max)	≤ 25.4 mm
Tubing Length (Max)	≤ 102 mm

#### Product Availability

Heat Shrink Equipment Region	Worldwide
------------------------------	-----------

#### Other

Equipment Processing Type	Shuttle
Heat Shrink Equipment Application	Battery, Cable Assembly, Hose & Pipe Protection, In-Line Splice, Ring Terminal, SolderSleeves, Stub Splice
Tooling Type	Holding Tool
Substrate Outside Diameter Max	26 mm



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts

TE Part # 1-2389761-2 RBK-TEMP-CAL-KIT-UHI	TE Part # 8-2410402-6 LOWER HEATER, W/ K TYPE T/C	TE Part # 8-2410402-7 UPPER HEATER, W/O K TYPE T/C
---	--	---

## Documents

[Agency Approvals](#)

[CE Declaration of Conformity](#)



[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

French

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

English

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

German

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)

[CE Declaration of Conformity](#)