


Within Series Adaptor 31_SMP-50-0-5/111_N

Description

Adaptor jack/jack
SMP jack (female) / SMP jack (female)

Interface standard
Series SMP - MIL-STD-348 SMP



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 40 GHz

Mechanical Data

Weight 0.000209 kg

Environmental Data

Operating temperature -55 °C to 125 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Interface - SMP jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PTFE (Polytetrafluoroethylene)	

Interface - SMP jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Outline drawing DOU-00316638

Ordering Information

Single package 31_SMP-50-0-5/111_NE