

LC1F4002

TeSys F contactor-2P(2 NO)-AC-1 <= 440V 500A with coil LX1/LX9 -48...1000V AC 40/400Hz, LX4 -48...440V DC, LXE -100...250V AC 50/60Hz or 100...380V DC



Main

Range	TeSys
Product name	TeSys F
Product or Component Type	Contacteur
Device short name	LC1F
Contacteur application	Resistive load
Utilisation category	AC-1
Poles description	2P
Power pole contact composition	2 NO
[Ue] rated operational voltage	<= 1000 V AC 50/60 Hz <= 460 V DC
[Ie] rated operational current	500 A 104 °F (40 °C)) <= 440 V AC AC-1

Complementary

[Uc] control circuit voltage	48...1000 V AC 40...400 Hz with LX1/LX9 coil 48...440 V DC with LX4 coil 100...250 V AC 50/60 Hz with LXE coil 100...380 V DC with LXE coil
[Uimp] rated impulse withstand voltage	8 kV
Overtoltage category	III
[Ith] conventional free air thermal current	500 A 104 °F (40 °C)
Irms rated making capacity	4000 A AC IEC 60947-4-1
Rated breaking capacity	3200 A IEC 60947-4-1
[Icw] rated short-time withstand current	3600 A 104 °F (40 °C) - 10 s 2400 A 104 °F (40 °C) - 30 s 1700 A 104 °F (40 °C) - 1 min 1200 A 104 °F (40 °C) - 3 min 1000 A 104 °F (40 °C) - 10 min
Associated fuse rating	400 A aM <= 440 V 500 A gG <= 440 V
Average impedance	0.26 mOhm - Ith 500 A 50 Hz
[Ui] rated insulation voltage	1000 V IEC 60947-4-1 1500 V VDE 0110 group C
Power dissipation per pole	65 W AC-1
Control circuit voltage limits	Operational 0.85...1.1 Uc AC 40...400 Hz Drop-out 0.3...0.5 Uc AC 40...400 Hz Operational 0.85...1.1 Uc DC Drop-out 0.2...0.35 Uc DC Operational 85...275 V AC 50/60 Hz Drop-out 0...60 V AC 50/60 Hz Operational 85...418 V DC Drop-out 0...45 V DC
Heat dissipation	14 W 2.2...5.5 W
Operating time	40...75 ms closing with LX1/LX9 coil 100...170 ms opening with LX1/LX9 coil 50...60 ms closing with LX4 coil 45...60 ms opening with LX4 coil 40...80 ms closing with LXE coil 6...54 ms opening with LXE coil

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mounting Support	Plate
Standards	JIS C8201-4-1 IEC 60947-4-1 IEC 60947-1 EN 60947-4-1 EN 60947-1
Product Certifications	CB ABS DNV RMRoS LROS (Lloyds register of shipping) BV RINA UL CSA UKCA
Connections - terminals	Power circuit bar 2 30 x 5 mm Power circuit lugs-ring terminals 2 0.23 in ² (150 mm ²) Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²)flexible without cable end Control circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²)flexible with cable end Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²)flexible with cable end Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²)solid without cable end Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) Control circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) Control circuit screw clamp terminals 1.0 0.00...0.00 in ² (0.2...2.5 mm ²)flexible without cable end Control circuit screw clamp terminals 1.0 0.00...0.00 in ² (0.25...2.5 mm ²)flexible with cable end Control circuit screw clamp terminals 1.0 0.00...0.00 in ² (0.2...2.5 mm ²)solid without cable end
Tightening torque	Power circuit 309.78 lbf.in (35 N.m) Control circuit 10.62 lbf.in (1.2 N.m) Control circuit 5.31 lbf.in (0.6 N.m)
Mechanical durability	10 Mcycles
Inrush power in VA	1000...1150 VA, 40..400 Hz cos phi 0.9 (at 68 °F (20 °C))with LX1/LX9 coil 920...1140 VA (at 68 °F (20 °C))with LX4 coil 360...470 VA, 50/60 Hz cos phi 0.5 (at 68 °F (20 °C))with LXE coil 410...450 VA (at 68 °F (20 °C))with LXE coil
Hold-in power consumption in VA	12...18 VA 4...7.5 VA 4.5...7.0 VA 2.5...4.0 VA
Maximum operating rate	2400 cyc/h 131 °F (55 °C)
Compatibility code	LC1F

Environment

IP degree of protection	IP20 front face with shrouds IEC 60529 IP20 front face with shrouds VDE 0106
Protective treatment	TH
Ambient Air Temperature for Operation	23...131 °F (-5...55 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Permissible ambient air temperature around the device	-40...158 °F (-40...70 °C)
Operating altitude	9842.52 ft (3000 m) without derating
Mechanical robustness	Vibrations contactor open1.5 Gn, 5...300 Hz Vibrations contactor closed5 Gn, 5...300 Hz Shocks contactor open6 Gn for 1/2 sine wave (11 ms) Shocks contactor closed15 Gn for 1/2 sine wave (11 ms)
Height	8.11 in (206 mm)
Width	8.39 in (213 mm)
Depth	8.62 in (219 mm)
Net Weight	17.64 lb(US) (8 kg)

Ordering and shipping details

Category	22336-CTR,F-LINE,AC,OPEN,NONREV
Discount Schedule	I12
GTIN	3389110227000
Nbr. of units in pkg.	1
Package weight(Lbs)	15.87 lb(US) (7.2 kg)
Returnability	No
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	9.45 in (24.0 cm)
Package 1 width	9.84 in (25.0 cm)
Package 1 Length	12.20 in (31.0 cm)
Unit Type of Package 2	P06
Number of Units in Package 2	10
Package 2 Weight	179.68 lb(US) (81.5 kg)
Package 2 Height	30.31 in (77.0 cm)
Package 2 width	31.50 in (80.0 cm)
Package 2 Length	23.62 in (60.0 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------