



X2 pro 10

10" HMI with iX runtime

1024 × 600 pixel (16:9)
TFT-LCD touch screen
1.5 GB application memory
Ethernet 2x100 Mbit
-10°C to +60°C operating temperature
CE, FCC, KCC, UL approvals
DNV GL, KR, LR, ABS, CCS, BV, NK, RS marine approvals

Facts

General description

Part number	630000305
Life cycle status	Active
Warranty	2 year

Certifications

General	CE, FCC, KCC
Marine	KR, LR, ABS, BV, CCS, NK, DNV GL, RS
Safety	UL 61010-1, UL 61010-2-201, CAN/CSA-C22.2 No. 61010-1, CAN/CSA-C22.2 No. 61010-2-201

Mechanical

Mechanical size	292 x 194 x 52mm
	Panel Mount, VESA 75 x 75
	1million finger touch operations
Touch type	Resistive
Cut-out size	275 x 177mm
Weight	1.65 kg
Housing material	Powder-coated aluminum, Gray

Power

Input voltage	24 V DC (18 to 32 VDC) CE: The power supply must conform with the requirements according to IEC 60950 and IEC 61558-2-4. UL and cUL: The power supply must conform with the requirements for class II power supplies.
Power consumption (max)	21.6W
Input fuse	Internal DC fuse
CPU	i.MX6DualLite, Dual Cortex-A9 1.0GHz 512kBL2cache
RAM	1 GB
FLASH	2GB SSD(eMMC), 1.5GB free for application

Display

Size diagonal	10.1" diagonal
Resolution	1024x600 pixels
Backlight	LED Backlight
Backlight life time	50000 hours
Backlight brightness	500 cd/m2
Backlight dimming	Industrial Dimming
Display type	TFT-LCD with LED backlight

Drivers

ABB - COMLI Master (5.7.2)
ABB - COMLI Slave (4.11.0)
ABB - TotalFlow (5.2.1)
Allen Bradley - ControlLogix Ethernet IP (4.24.1)
Allen Bradley - DF1 (5.8.0)
Allen Bradley - DH485 (4.6.2)
Allen Bradley - MicroLogix Ethernet (5.6.0)
Allen Bradley - SLC5/PLC5 Ethernet (5.4.0)
Altus - Alnet I (5.8.0)
Animatics - SmartMotor (5.2.1)

More drivers ▼

Smart Engineering Resources

Serial communication

Number of serial ports	1 Port 9pin DSUB
Serial port 1	RS 232 (RTS/CTS)
Serial port 2	RS422/485
Serial port 3	RS485 (only if COM 2 is RS485)

Ethernet communication

Number of Ethernet ports	2
Ethernet port 1	1x10/100 Base-T (shielded RJ45)
Ethernet port 2	1x10/100 Base-T (shielded RJ45)

	1
	0.5 MBit
	0.5 MBit

Expansion interface

Expansion port	Yes, cIX expansion module
SD card	SD and SDHC
USB	2xUSB 2.0 500mA

Environmental

Operating temperature	-10°C to +60°C
Storage temperature	-20°C to +70°C
Shock	15g, half-sine, 11ms according to IEC60068-2-27
Vibration	1g, according to IEC 60068-2-6, Test Fc
Sealing front	IP65, NEMA 4X/ 12 and UL 50E Type 4X/ 12
Sealing back	IP20
Humidity	5% - 85% non-condensed
Altitude (max)	< 3000m

Lenze - LECOM A/B (5.6.0)
LS Industrial System - Glofa (5.3.0)
LS Industrial System - Master K (5.4.0)
Matsushita - MEWTOCOL-COM (5.9.2)
Mitsubishi Electric - Alpha2 (5.7.0)
Mitsubishi Electric - A-series (C24) (5.6.0)
Mitsubishi Electric - A-series (CPU) (5.10.0)
Mitsubishi Electric - A-series (E71) (5.4.0)
Mitsubishi Electric - Freqrol FR-A PLC (5.8.2)
Mitsubishi Electric - FX Series A/DI/DO (5.10.0)

