

Safe-IT Multi-Device UV Charging Station, Hospital-Grade, 16 USB Ports, iPad and Android Tablets, Antimicrobial, White

MODEL NUMBER: CS16USBWHG



Charges, syncs, secures, organizes and sanitizes up to 16 USB devices in healthcare, education, retail, warehouse and office settings.

Features

Wall-Mount Charging Cabinet Accommodates up to 16 USB Mobile Devices This 120V charging station provides USB charging, secure storage, cord management and surface sanitization for as many as 16 iPad, iPod, iPhone, Android, Surface, Kindle and other USB tablets and smartphones. The USB ports deliver the fastest charging supported by each connected device, up to 2.4A per port. A USB uplink port connects to a host computer for wired syncing. The tablet charging station is recommended for healthcare facilities, classrooms, businesses, government agencies, restaurants, hotels and anywhere else that uses mobile devices on a daily basis.

UV Light Helps Sanitize Devices without Potentially Dangerous Heat, Liquids or Chemicals The CS16USBWHG helps reduce the presence of germs on Chromebooks, laptops and tablets. Built-in ultraviolet lights help disinfect electronic devices at the touch of a button by destroying most microbes without the use of damaging heat, liquids or chemicals. The germicidal UVC bupounds are on a timer to control the amount of UV exposure the devices receive. An LED on the exterior of the cabinet indicates when the doors are closed and the start button can be pressed to activate the 10-minute timer. A second LED indicates when the UVC lights are on. If a door is opened during sanitization, the lights automatically shut off for safety.

Exclusive Antimicrobial Protection Inhibits the Growth of Bacteria The charging cabinet's interior and exterior surfaces are protected by an antimicrobial coating which helps prevent the growth of bacteria, viruses, fungi, mold and mildew. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Locking Steel Enclosure Keeps Valuable Equipment Safe and Secure Constructed from heavy-duty steel, this charging cabinet provides safe, secure storage. The split front doors lock with the included keys to help prevent theft, damage and tampering. For extra security, the front door can be fastened with a user-supplied padlock. Flow-through ventilation helps protect against overheating, and the specially coated shelves help prevent device scratches and scuffs.

Mounts Easily to the Wall of a Nurse's Station, Classroom or Back Office Four rear keyhole cutouts allow efficient wall mounting. Cutouts accommodate M5 or 3/16-inch bolts (not included) and are spaced 16 inches apart horizontally and 12 inches vertically to match standard wall studs. The CS16USBWHG

Highlights

- 16 internal USB-A ports charge mobile devices with optimum charge level up to 2.4A
- Ultraviolet (UVC) lights help disinfect devices without use of damaging heat or chemicals
- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Steel enclosure locks with included keys to discourage theft, damage and tampering
- 10 ft. (3 m) cord with NEMA 5-15P HG plug allows great flexibility in reaching AC outlets

Applications

- Charge up to 16 Apple, Android, Microsoft, Amazon and other USB tablets and smartphones in medical facilities, schools, businesses and government organizations that rely on the daily use of mobile devices
- Sanitize your devices with ultraviolet light to reduce the presence of germs

Package Includes

- CS16USBWHG Hospital-Grade 16-Device UV Charging Cabinet, White
- (2) Keys
- Owner's manual

also supports stationary desktop or floor placement installations. You can also convert it to a mobile cart with the optional non-antimicrobial CSHANDLEKIT2 (sold separately), and roll it where needed.

Well-Organized to Avoid Confusing Cable Clutter Cables and connectors run through strain relief bushings, keeping them organized and out of the way, and are protected by blanking panels. Adjustable dividers accommodate up to 16 devices. Front doors open at least 180 degrees to allow maximum access to the interior. Access grommets allow the 10-foot (3-meter) cord with hospital-grade NEMA 5-15P plug to extend through either side of the cart, allowing great flexibility in reaching AC outlets.

Specifications

OVERVIEW	
UPC Code	037332240132
Product Type	Multi-Device Charger
Charging Form Factor	Stationary Cabinet
Functions	Charge; Secure; Sync; Sanitize
Device Compatibility	Tablet; Phone
Device Slots	16
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Connection Type	C14 inlet with 110-120V AC compatibility. Also accepts user-supplied country-specific AC cordsets
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
POWER	
Power Consumption (Watts)	56
CHARGING	
Number of Charging Ports	16
Total Charging Amps	40A
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Overcharge Protection	Yes
Charging Amps per Port	2.4A
PHYSICAL	

Color	White
Material of Construction	Steel
Shipping Dimensions (hwd / in.)	24.53 x 33.66 x 23.62
Shipping Weight (kg)	50.50
Slot Dimensions (hwd / in.)	10.6 x 1.5 x 15.4
Slot Dimensions (hwd / mm)	268.1 x 38.2 x 390.5
Unit Dimensions (hwd / in.)	18.800 x 30.330 x 20.200
Unit Dimensions (hwd / cm)	47.75 x 77.04 x 54.86
Unit Weight (lbs.)	84.66
Unit Weight (kg)	38.40
Number of Shelves	1
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Cord Management	No
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	Yes
Flow-Through Ventilation	Yes
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
UV Sterilization	Yes
Locking	Yes
Lock Type	Key; Padlock (User Supplied)
STANDARDS & COMPLIANCE	
Product Certifications	NOM (Mexico); UL 60950-1
Product Compliance	RoHS; CE (Europe); EIA/ECA-310-E; REACH; FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.