


Enclosure Mini Panel for 4 Copper/Fiber Cassettes, 1U

MODEL NUMBER: **N484-01U-MINI**



1U rack-mount enclosure panel allows you to add up to 4 high-density copper or fiber cassettes to your rack installation.

Features

1U Copper/Fiber Enclosure Adds Up to 4 High-Density Cassettes to Your Rack Installation Insert up to four N484-Series copper and/or fiber cassettes (sold separately) into this cost-effective enclosure panel. Mounting in just 1U of space in an EIA-standard 19-inch rack, the compact N484-01U-MINI includes no protruding front door or rear cable management, which allows more inside rack space. It is ideal for a wide range of singlemode and multimode applications in small and medium enterprise environments where equipment is connected in up to three adjacent racks. The fully passive mini panel adds no heat or cooling load.

Easily Accommodates a Variety of Cassette Types The heavy-duty steel N484-01U-MINI houses as many as four N484-Series cassettes, including RJ45 and SFP+ copper and LC duplex and MTP/MPO fiber, and 48 ports within its 1U chassis. In the case of fiber cassettes, the panel lets you interconnect any combination of 10 Gb, 40 Gb and 100/120 Gb network equipment in a simple, elegant and highly flexible way. It seamlessly connects to your existing cabling infrastructure and supports a wide range of applications and protocols in high-density telecom and data center environments.

Highlights

- 1U chassis accepts fiber and copper cassettes, including RJ45, SFP+, LC and MTP/MPO
- Allows interconnection of any combination of 10 Gb, 40 Gb and 100/120 Gb fiber equipment
- Compact design eliminates front door and rear cable bar to allow more inside rack space
- Fully passive mini enclosure panel adds no heat or cooling load
- Ideal for single- and multimode applications in small/medium enterprise environments

Applications

Connect, organize and manage copper and fiber optic cable connections in your high-density telecom or data center environment

System Requirements

- Compatible with N484-Series copper and fiber cassettes

Package Includes

- N484-01U-MINI High-Density Copper/Fiber Enclosure Mini Panel
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332250438
Accessory Type	Pass-Through Panel
Technology	Cat5/5e; Cat6; Cat6a; Multimode
Firmware / Software Docs	
Offset Ports	No

PHYSICAL	
Primary Form Factor	Rackmount
Color	Black
Material of Construction	Aluminum, Steel
Rack Height	1U
Cassette Type	Panel Enclosure; Pass-through
Cassette Capacity	4
Rackmountable	Yes
Unit Dimensions (hwd / in.)	1.730 x 18.980 x 1.190
Unit Weight (lbs.)	1.37
Unit Weight (kg)	0.62
FEATURES & SPECIFICATIONS	
All-in-One Kit	No
Numbered Ports	No
Keystone Jacks	No
Built-in Cables	No
Color-Coded Connections	No
EIA/TIA 2/32 Spacing	No
Labeled Ports	No
Down-Angled Ports	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty