TRIPP-LITE

3-Phase 208V UPS + Input/Output Isolation Transformer Kit - 480V to 208V/208V to 480V, 30kVA/kW, External Batteries Required

MODEL NUMBER: S3M30K-30KWR4T







Combines step-down and step-up transformers with a UPS to provide isolation protection and clean, reliable backup power to support connected loads.

Features

30kVA/kW 3-Phase UPS and Input/Output Isolation Transformers Combined into One Kit

This SmartOnline® kit for 480V IT loads combines Tripp Lite's S3M30K 208/220/120/127V Double-Conversion UPS, a 480V (Delta) to 208V (Wye) input isolation step-down transformer and a 208V (Wye) to 480V (Wye) output auto step-up transformer into one convenient package. The S3M30K-30KWR4T combo kit is ideally suited for vital applications in banking, education, healthcare, government and manufacturing sectors.

Battery Backup and VFI Operation Protect Critical Loads

The IGBT UPS supports the continuous availability of your most important operational and IT equipment loads through all power conditions, providing a compact backup power platform that's easy to manage and inexpensive to operate. Sophisticated voltage- and frequency-independent (VFI) operation and advanced IGBT rectifier technology with DSP control deliver reliable output power quality.

Complete Step-Down/Step-Up and Isolation Protection That Prevents Power Disruption

The dual transformers offer line isolation and protection to the UPS system and its load. They isolate the UPS and connected components from line surges and spikes caused by utility power disruptions that can damage equipment or corrupt data.

Best-in-Class Footprint for Easy Integration into Your Network Application

The compact design lets you install the steel housings in spaces that would otherwise have required expensive retrofitting. By achieving their condensed size without compromising runtime, reliability or functionality, this combination UPS/transformer kit is recommended for data centers, colocation facilities and edge computing environments that require high efficiency, high performance and clean, reliable power protection, while preserving as much space as possible for revenue-generating server racks.

Efficient UPS Operation and Design Reduces Cost of Ownership

The UPS features ENERGY STAR 2.0-certified technology that provides high operational efficiency to save on utility and cooling costs, as well as protect the environment. It achieves 94% efficiency in doubleconversion mode and up to 98% in ECO mode, reducing your power and cooling costs. Unity output power factor (1.0) lets you support more equipment. A low THDi (<3%) improves generator compatibility. A low THDv (2%) and active power factor correction with DSP control improve output performance.

Highlights

- Dual 30kVA/kW 480V transformers for government, healthcare and corporate settings
- ENERGY STAR 2.0-certified UPS efficiency up to 98% helps reduce utility/cooling costs
- Unity output power factor (1.0) allows support of more equipment without overloading
- Optional WEBCARDLXMINI network card allows costeffective remote management 24/7
- Rugged steel housings with compact footprint come ready for installation

Applications

- Fit transformer, UPS and batteries in best-in-class footprint to save space for revenue-generating equipment
- Protect equipment in government, healthcare, manufacturing, corporate and other settings that have 480V electrical mains and 480V IT loads
- Maintain server-room operations during all power conditions, including short blackouts

Package Includes

- S3M30K 3-Phase 208/220/120/127V 30kVA/kW Double-Conversion UPS
- S3MT-30KWR480V 3-Phase 30kVA Input/Output Isolation Transformers
- Parallel UPS cable
- USB cable
- RS-232 cable
- (4) Bottom skirts
- (24) Screws
- Owner's manuals

TRIPP-LITE

Transformer Performs with High Efficiency up to 97.5%

Not only does the S3MT-30KWR480V wrap-around transformer offer up to 97.5 percent efficiency, it also is very quiet with a noise profile less than 65 dBA. Built-in circuit breakers on both transformers help prevent dangerous power overloads. Four ball-bearing cooling fans help prevent overheating. An overheat-sensing relay and switch combine with red alarm indicators to provide over-temperature warning and overheating protection.

External Batteries Supply Reliable Backup with Expandable Runtime Options

The S3M30K uses external battery cabinets, including BP240V40/40L, BP240V65/65L and BP240V100 (sold separately), to provide backup support in case of a power failure. These cabinets are available with or without internal batteries. No internal batteries are included with the S3M30K. A one-touch cold-start button powers up the UPS with battery power only.

Remote Network Monitoring and Control Available 24 Hours a Day

The optional Java-free WEBCARDLXMINI network management card (sold separately) enables remote UPS management through embedded HTML5 web, SSH/telnet and SNMP interfaces, as well as integration with a wide range of network management systems and DCIM platforms. WEBCARDLXMINI also supports EnviroSense2 modules (sold separately), which monitor temperature, humidity and other environmental factors.

Specifications

OVERVIEW		
OVERVIEW		
UPC Code	037332253255	
Transformer Type	Input Step Down/Output Step Up	
UPS Type	On-Line	
INPUT		
Nominal Input Voltage(s) Supported	480V 3-PH Delta	
UPS Input Connection Type	Hardwire	
Input Phase	3-Phase	
OUTPUT		
Output Capacity (VA)	30000	
Output Capacity (kVA)	30	
Nominal Output Voltage(s) Supported	120/208V 3-PH Wye	
PHYSICAL		
Primary Form Factor	Tower	
STANDARDS & COMPLIANCE		
Product Certifications	UL 1778	
WARRANTY & SUPPORT		



1000 Eaton Boulevard Cleveland, OH 44122 United States

Product Warranty Period (Worldwide)	2-year limited warranty
Product Warranty Period (U.S. & Canada)	2-year limited warranty



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.