

In-Line PoE Surge Protector - 1 Gbps, Cat5e/6, Metal Case, IEC Compliant, TAA

MODEL NUMBER: **B110-SP-POE**



Use in your digital signage network to protect Power over Ethernet (PoE) equipment from surges, ESD and cable discharge events.

Features

In-Line Surge Protector Keeps Your Power Over Ethernet (PoE) Equipment Safe

Ideal for home/corporate security systems, home theaters, trade shows and other digital signage applications, the B110-SP-POE protects connected equipment from damage caused by electrostatic discharge (ESD) and cable discharge events. Just connect it between your source and network equipment using Cat5/5e/6 cables, such as N001-Series snagless patch cables (sold separately). **Note:** two B110-SP-POE surge protectors are required to protect both source and device.

Your Last Defense Against Intruding Voltage Spikes

Solid-state silicon-avalanche diode technology features low clamping voltage, providing superior protection against ESD and super-fast response time under one nanosecond. Both mid-span and end-span PoE are supported. The B110-SP-POE meets the following IEC/EN regulations: IEC 61000-4-2 / IEC 61000-4-5 (ESD) 30kV (Air, Contact) and EN 61000-4-5 5kA (8/20s) / 4kV (10/700s).

Ready to Use Right from the Package, So You Can Plug and Play Immediately

This PoE in-line surge protector meets 802.3af and 802.3at IEEE standards, while supporting data transmission speeds up to 1 Gbps. No software, drivers or external power supply is required. The compact metal housing is designed to endure in applications where static discharge is likely to occur. Mounting hardware is included for convenient installation where needed. Be sure the distance between the B110-SP-POE and the equipment it is protecting is no more than 300 feet.

TAA-Compliant for GSA Schedule Purchases

The B110-SP-POE is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

| OVERVIEW | |
|--------------|-----------------|
| UPC Code | 037332217875 |
| Product Type | Surge Protector |

Highlights

- Easy to connect between PoE source and device using standard Cat5/5e/6 cabling
- Rapid reaction time under 1 ns helps prevent damage from power surges
- Supports 802.3af/802.3at IEEE standards and data transmission speeds up to 1 Gbps
- Plug-and-play operation with no software required for easy, immediate installation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

Protect a Power over Ethernet (PoE) device's inputs and outputs against damage from electrostatic discharge or power surge

Package Includes

- B110-SP-POE In-Line 1G PoE Surge Protector
- Grounding wire, 1 ft.
- (4) Mounting screws
- (4) Screw anchors
- Grounding wire screw
- Quick Start Guide

| | |
|--|-----------------------|
| Technology | Cat5/5e; Cat6; PoE |
| INPUT | |
| Input Cord Length (ft.) | 0 |
| Right-Angle Plug | No |
| Input Cord Length (m) | 0.00 |
| OUTPUT | |
| Output Receptacles | Network |
| Right-Angle Outlets | No |
| POWER | |
| Power Over Cable (PoC) Support | Yes |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LED(s) | No |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 0 |
| Automatic Shut-Off | No |
| DATALINE SURGE SUPPRESSION | |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | Yes |
| Telephone/DSL Protection | No |
| PHYSICAL | |
| Material of Construction | Aluminium |
| Housing Color | Black |
| Rackmountable | No |
| Shipping Dimensions (hwd / in.) | 1.54 x 4.53 x 4.25 |
| Shipping Dimensions (hwd / cm) | 3.91 x 11.51 x 10.80 |
| Shipping Weight (lbs.) | 0.37 |
| Shipping Weight (kg) | 0.17 |
| Unit Dimensions (hwd / in.) | 2.630 x 3.430 x 1.060 |
| Unit Dimensions (hwd / cm) | 67 x 87 x 27 |
| Unit Packaging Type | Box |
| Unit Weight (lbs.) | 0.28 |

| | |
|--------------------------------------|---|
| Unit Weight (kg) | 0.13 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 14° to 167°F (10° to 75°C) |
| Storage Temperature Range | -40° to 194°F (-40° to 90°C) |
| Relative Humidity | 0% to 95% RH, Non-Condensing |
| COMMUNICATIONS | |
| Network Compatibility | 1 Gbps (Gigabit) |
| IEEE Standards Supported | 802.3af; 802.3at |
| CONNECTIONS | |
| Side A - Connector 1 | RJ45 (FEMALE) |
| Side B - Connector 1 | RJ45 (FEMALE) |
| FEATURES & SPECIFICATIONS | |
| Rotatable Outlets | No |
| Antimicrobial | No |
| Driver Required | No |
| Recommended Category Cable | Cat5e, Cat6 Cables |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |