


## DC Power Supply for N785-CH12 Media Converter Chassis, 75W

MODEL NUMBER: N785-CH75W-DC



75W DC power supply provides primary or redundant power to your media converter installation.

### Features

#### Powers Your N785-CH12 12-Port Media Converter Chassis

This 75-watt DC power supply works with the N785-CH12 media converter chassis to provide primary or redundant power. The N785-CH12 comes with a pre-installed AC power supply, but you can swap it out for the N785-CH75W-DC if you prefer DC power. This DC power supply can be used with any DC power source up to 48V 3A. A second DC power supply is also recommended to provide redundant power that helps prevent unwanted and expensive downtime. **Note:** Only one type of power supply should be used with the N785-CH12. Do not mix DC and AC power supplies.

## Specifications

| OVERVIEW                                  |                          |
|---|--------------------------|
| UPC Code                                  | 037332267078             |
| Accessory Type                            | Power Supply             |
| Accessory Class                           | Networking Accessories   |
| INPUT                                     |                          |
| AC Power Adapter Plug(s)                  | NEMA 5-15P North America |
| AC Power Adapter Input Specs (V / Hz / A) | 48V / 3A                 |
| AC Power Adapter Output Specs (V / A)     | 12V / 6.5A               |
| AC Power Adapter Cord Length (ft.)        | 6                        |
| AC Power Adapter Cord Length (m)          | 1.83                     |

### Highlights

- Supplies DC power to a media converter installation using N785-CH12
- Multiple power supplies provide primary and redundant power to prevent downtime

### System Requirements

N785-CH12 Media Converter Chassis

### Package Includes

N785-CH75W-DC 75W DC Power Supply

| POWER                                |   |
|--------------------------------------|---|
| Power Source Type                    | AC Adapter  |
| PHYSICAL                             |   |
| Power Cord Color                     | Black   |
| Unit Dimensions (hwd / in.)          | 5.240 x 2.320 x 9.060   |
| Unit Dimensions (hwd / cm)           | 13.3 x 5.9 x 23.0   |
| Unit Packaging Type                  | Box   |
| ENVIRONMENTAL                        |   |
| Operating Temperature Range          | 32° to 122°F (0° to 50°C)                                       |
| Storage Temperature Range            | 14° to 158°F (-10° to 70°C)                                     |
| Operating Humidity Range             | 10% to 90%  |
| Storage Humidity Range               | 5% to 95%   |
| FEATURES & SPECIFICATIONS            |   |
| IP68 Rated                           | No  |
| IP20 Rated                           | No  |
| Auto MDIX Support                    | No  |
| STANDARDS & COMPLIANCE               |   |
| External Power Supply Certifications | CE; FCC; RoHS   |
| Product Compliance                   | RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT                   |   |
| Product Warranty Period (Worldwide)  | 3-year limited warranty   |