

Han 4A-SC-M




Image is for illustration purposes only. Please refer to product description.

Part number	09 20 004 4701
Specification	Han 4A-SC-M
HARTING eCatalogue	https://b2b.harting.com/09200044701

Identification

Category	Inserts
Series	Han-Brid [®]
Identification	Han [®] 4 A SC
Description of the contact	for FO

Version

Gender	Male
Size	3 A
Number of contacts	4
Details	Please order contacts separately.

Technical characteristics

Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

Material properties

China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	2
Net weight	6.08 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440205 Contact insert for industrial connectors