

M12 D-cod 4-pol st/st m/m Rail 6.0m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 222 2011 060
Specification	M12 D-cod 4-pol st/st m/m Rail 6.0m
HARTING eCatalogue	https://b2b.harting.com/09482222011060

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Straight Overmoulded
Connector 2	M12 D-coding Male Straight Overmoulded
Type of cable	Copper cable (round)
Description of the cable	for railway applications

Version

Cable length	6 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +85 °C unmoved -25 ... +70 °C moved



Pushing Performance

Technical characteristics

Cable diameter	6.6 mm ± 0.2 mm
Minimum bending radius	6x Cable diameter (repeated bending) 5x Cable diameter (singular bending)
Impedance	100 Ω ±5 %

Material properties

Material (cable)	Elastomer
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 45545-2
----------------	------------

Commercial data

Packaging size	10
Net weight	434.2 g
Country of origin	Romania
European customs tariff number	85444290
eCl@ss	27060390 Ready-made data cable (unspecified)