

Female contact crimp Pack d0,6 AWG23-26



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9021
Specification	Female contact crimp Pack d0,6 AWG23-26
HARTING eCatalogue	https://b2b.harting.com/21011009021

Identification

Category	Contacts
Series	har-speed
Type of contact	Crimp contact

Version

Gender	Female
Manufacturing process	Turned contacts
Performance level	1

Technical characteristics

Conductor cross-section	0.13 ... 0.25 mm ²
Conductor cross-section	AWG 26 ... AWG 23

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



Pushing Performance

Material properties

REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a

Commercial data

Packaging size	100
Net weight	0.11 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors