

## M12 PushPull 8-pole A-coded male



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 821 1830
Specification	M12 PushPull 8-pole A-coded male
HARTING eCatalogue	<a href="https://b2b.harting.com/21038211830">https://b2b.harting.com/21038211830</a>

### Identification

Category	Connectors
Series	Circular connectors M12
Identification	PushPull
Element	Cable connector
Specification	Straight

### Version

Termination method	Crimp termination
Gender	Male
Locking type	PushPull
Shielding	Shielded
Number of contacts	8
Coding	A-coding
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm <sup>2</sup>
Conductor cross-section	AWG 26 ... AWG 22
Wire outer diameter	≤1.65 mm
Rated current	2 A
Rated voltage	30 V AC 30 V DC
Rated impulse voltage	0.8 kV



Pushing Performance

## Technical characteristics

Pollution degree	3
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Ambient temperature	-40 ... +85 °C
Mating cycles	$\geq 500$
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	5.7 ... 8.8 mm
Isolation group	I ( $600 \leq \text{CTI}$ )

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight 6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521

## Commercial data

Packaging size	1
Net weight	60.2 g
Country of origin	Romania



Pushing Performance

## Commercial data

European customs tariff number 85369010

eCl@ss 27440102 Circular connector (for field assembly)