

M12-SD-CC-IDC-4P-DCOD-F-STR-SHLD



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 382 2400
Specification	M12-SD-CC-IDC-4P-DCOD-F-STR-SHLD
HARTING eCatalogue	https://b2b.harting.com/21033822400

Identification

Category	Connectors
Series	Circular connectors M12
Identification	Slim Design
Element	Cable connector
Specification	Straight

Version

Termination method	HARAX [®] connection technology
Gender	Female
Locking type	Screw locking
Shielding	Shielded
Number of contacts	4
Coding	D-coding
Details	For Fast Ethernet applications only

Technical characteristics

Conductor cross-section	0.34 mm ²
Conductor cross-section	AWG 22
Wire outer diameter	≤1.6 mm
Rated current	4 A
Rated voltage	50 V
Rated impulse voltage	1.5 kV
Pollution degree	3



Pushing Performance

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	15
Ambient temperature	-40 ... +85 °C
Mating cycles	≥ 500
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	5.7 ... 8.8 mm
Isolation group	I ($600 \leq \text{CTI}$)

Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	53.4 g
Country of origin	Romania



Pushing Performance

Commercial data

European customs tariff number 85389099

eCl@ss 27440102 Circular connector (for field assembly)