

## Han-Yellock F-c 0.37mm<sup>2</sup> (Ag)




Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 11 05 000 6201  |
| Specification      | Han-Yellock F-c 0.37mm <sup>2</sup> (Ag)  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/11050006201">https://b2b.harting.com/11050006201</a> |

### Identification

|                 |                          |
|-----------------|--------------------------|
| Category        | Contacts                 |
| Series          | Han-Yellock <sup>®</sup> |
| Type of contact | Crimp contact            |

### Version

|                       |                 |
|-----------------------|-----------------|
| Gender                | Female          |
| Manufacturing process | Turned contacts |

### Technical characteristics

|                         |                               |
|-------------------------|-------------------------------|
| Conductor cross-section | 0.14 ... 0.37 mm <sup>2</sup> |
| Conductor cross-section | AWG 26 ... AWG 22             |
| Operating current       | ≤20 A                         |
| Contact resistance      | ≤2 mΩ                         |
| Stripping length        | 6.5 mm                        |

### Material properties

|                             |  |
|-----------------------------|--|
| Material (contacts)         | Copper alloy   |
| Surface (contacts)          | Silver plated  |
| RoHS                        | compliant with exemption                               |
| RoHS exemptions             | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                  | compliant with exemption                               |
| China RoHS                  | 50   |
| REACH Annex XVII substances | No   |



Pushing Performance

## Material properties

|                            |                                      |
|----------------------------|--------------------------------------|
| REACH ANNEX XIV substances | No                                   |
| REACH SVHC substances      | Yes                                  |
| REACH SVHC substances      | Lead                                 |
| ECHA SCIP number           | b51e5b97-eeb5-438b-8538-f1771d43c17d |

## Specifications and approvals

|                |                         |
|----------------|-------------------------|
| Specifications | EN 60664-1<br>IEC 61984 |
|----------------|-------------------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 100  |
| Net weight                     | 0.49 g                                     |
| Country of origin              | Germany                                    |
| European customs tariff number | 85366990                                   |
| eCl@ss                         | 27440204 Contact for industrial connectors |