

Han 10HvE-kg-QB-M32



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---------------------------------------------------------------------------------------|
| Part number | 19 34 010 0732 |
| Specification | Han 10HvE-kg-QB-M32 |
| HARTING eCatalogue | https://b2b.harting.com/19340100732 |

Identification

| | |
|--------------------------|------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han Hv E [®] |
| Type of hood/housing | Cable to cable housing |
| Type | Low construction |

Version

| | |
|----------------------------|-----------------------------------------------------------------|
| Locking type | Double locking lever |
| Han-Easy Lock [®] | Yes |
| Size | 24 B |
| Version | Top entry |
| Cable entry | 1x M32 |
| Field of application | Special hoods/housings for Han Hv E [®] screw terminal |

Technical characteristics

| | |
|----------------------------------------|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| | |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Powder-coated |



Pushing Performance

Material properties

| | |
|------------------------------------------------------------|-----------------------------------------------------------|
| Colour (hood/housing) | RAL 7037 (dust grey) |
| Material (seal) | NBR |
| Material (locking) | Polycarbonate (PC) Stainless steel |
| Colour (locking) | RAL 7037 (dust grey) |
| Material flammability class acc. to UL 94 (locking levers) | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
| CE | Yes |

Commercial data

| | |
|--------------------------------|------------------------------------------|
| Packaging size | 1 |
| Net weight | 252.3 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| eCl@ss | 27440202 Shell for industrial connectors |