

DIN-Signal high current f, 40A press-in



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 03 000 6250 |
| Specification | DIN-Signal high current f, 40A press-in |
| HARTING eCatalogue | https://b2b.harting.com/09030006250 |

Identification

| | |
|----------------------------|-----------------------|
| Category | Contacts |
| Series | DIN 41612 |
| Type of contact | Press-in contact |
| Description of the contact | Straight |
| Contacts for | DIN 41612 Type M-flat |

Version

| | |
|-----------------------|--------------------------------------|
| Gender | Female contact for female connectors |
| Manufacturing process | Turned contacts |

Technical characteristics

| | |
|-------------------|-------|
| Operating current | ≤40 A |
| Performance level | 1 |
| Mating cycles | ≥500 |

Material properties

| | |
|-----------------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Noble metal |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |



Pushing Performance

Material properties

| | |
|----------------------------|--------------------------------------|
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| ECHA SCIP number | 339476a1-86ba-49e9-ab4b-cd336420d72a |

Specifications and approvals

| | |
|----------------|-----------|
| Specifications | DIN 41626 |
|----------------|-----------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 100 |
| Net weight | 1.06 g |
| Country of origin | Czechia |
| European customs tariff number | 85366990 |
| eCl@ss | 27440204 Contact for industrial connectors |

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques acc. to IEC 60512-5-2

