

Keystone Patch panel, unloaded



Part number	20 82 400 0002
Specification	Keystone Patch panel, unloaded
HARTING eCatalogue	https://b2b.harting.com/20824000002

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	preLink [®]
Element	Patch panel
Specification	Empty

Version

Size	Keystone version
Fixing	In 19" racks acc. to IEC/DIN EN 60 297-3-100 (DIN 41 494-1)

Technical characteristics

Limiting temperature	-40 +85 °C
Degree of protection acc. to IEC 60529	IP20
Transmission characteristics	Cat. 6 Class E up to 250 MHz
Data rate	10 Gbit/s
Vibration resistance	5.72 m/s² acc. to IEC 61373 Category 1 Class B
Shock resistance	$5~\mbox{g}$ / $30~\mbox{ms},$ $5~\mbox{shocks}$ / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (insert)	Steel sheet
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No



Material properties

REACH ANNEX XIV substances No
REACH SVHC substances No

Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	942 g
Country of origin	Czechia
European customs tariff number	85389099
eCl@ss	27440292 Connector component (accessories)