

Han 1HC-sti-AX (350A,35-70mm²)



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 001 2651
Specification	Han 1HC-sti-AX (350A,35-70mm ²)
HARTING eCatalogue	https://b2b.harting.com/09110012651

Identification

Category	Inserts
Series	Han [®] HC Modular
Identification	350

Version

Termination method	Axial screw termination
Gender	Male

Technical characteristics

Conductor cross-section	35 ... 70 mm ²
Wire outer diameter	≤19.5 mm
Rated current	350 A
Rated voltage	2,000 V
Rated impulse voltage	12 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Contact resistance	≤0.2 mΩ
Stripping length	19 ... 20 mm
Tightening torque	8 Nm @ 35 mm ² 10 Nm @ 50 mm ² 12 Nm @ 70 mm ²
Limiting temperature	-40 ... +125 °C



Pushing Performance

Technical characteristics

Mating cycles ≥500

Material properties

Material (insert)	Polycarbonate (PC) Polyamide (PA)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight 6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	1
Net weight	137 g
Country of origin	Romania
European customs tariff number	85359000
eCl@ss	27440205 Contact insert for industrial connectors