

## Han-Eco Mod.16-C-f. HTE/HSE



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 016 5406
Specification	Han-Eco Mod.16-C-f. HTE/HSE
HARTING eCatalogue	<a href="https://b2b.harting.com/19410165406">https://b2b.harting.com/19410165406</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® Modular
Type of hood/housing	Protection cover
Description of hood/housing	for hoods

### Version

Locking type	Double locking lever
Size	16 B

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



Pushing Performance

## Material properties

Material flammability class acc. to UL 94  
(locking levers) V-0

RoHS compliant

ELV status compliant

China RoHS e

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances No

## Specifications and approvals

Specifications IEC 61984  
EN 45545-2 R22: HL1, HL2, HL3  
EN 45545-2 R23: HL1, HL2, HL3  
EN 45545-2 R24: HL1, HL2, HL3

UL / CSA UL 1977 ECBT2.E235076  
CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size 1

Net weight 85.6 g

Country of origin Germany

European customs tariff number 85389099

eCl@ss 27440208 Cap for industrial connectors