



Main

Product	Tap box
Range	I-Line

Complementary

Rated Current	800...1600 A
Rated Operational Voltage	600 V AC/DC 50/60 Hz
Length	23.5 in (596.90 mm)
Height	28.2 in (716.28 mm)
Width	24 in (609.60 mm)
Mounting Mode	Horizontal
Number of Phases	3 phase
Protection Type	50 percent capacity integral ground bus
Wiring Configuration	4-wire
Wire Gauge	AWG 1/0...600 kcmil

Ordering and shipping details

Category	20197-PTB 1600A TAP BOX
Discount Schedule	PE8
GTIN	785901087434
Nbr. of units in pkg.	1
Package weight(Lbs)	266.00 lb(US) (120.656 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	23.50 in (59.7 cm)
Package 1 width	24.02 in (61 cm)
Package 1 Length	28.19 in (71.6 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------