

PushPull V4, power, 250V/16A, w/o cont.



Image is for illustration purposes only. Please refer to product description.

Part number	09 46 145 3421
Specification	PushPull V4, power, 250V/16A, w/o cont.
HARTING eCatalogue	https://b2b.harting.com/09461453421

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	Power
Element	Connector sets

Version

Termination method	Crimp termination
Locking type	PushPull
Shielding	Unshielded
Number of contacts	2
PE contact	Yes
Pack contents	Without contacts

Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm ² Stranded
Conductor cross-section	AWG 20 ... AWG 12 Stranded
Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Tightening torque	1.3 ... 1.5 Nm
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750



Pushing Performance

Technical characteristics

Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	4.5 ... 10 mm
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 2h/axis 5.72 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	25 g / 11 ms, 3 shocks / axis and direction 5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4) EN 45545-2 R26: HL1, HL2, HL3
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	1
Net weight	1 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)




Pushing Performance

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques acc. to IEC 60512-5-2



- ① Heating
 - ② Derating curve
 - ③ Derating curve 80%
- Conductor cross-section 2.5 mm²