



## Main

Product	Tap box
Range	I-Line

## Complementary

Rated Current	800...1600 A
Rated Operational Voltage	600 V AC/DC 50/60 Hz
Length	23.5 in (596.90 mm)
Height	28.2 in (716.28 mm)
Width	24 in (609.60 mm)
Mounting Mode	Vertical
Number of Phases	3 phase
Protection Type	50 percent capacity integral ground bus
Wiring Configuration	4-wire
Wire Gauge	AWG 1/0...600 kcmil

## Ordering and shipping details

Category	20197-PTB 1600A TAP BOX
Discount Schedule	PE8
GTIN	785901159384
Nbr. of units in pkg.	1
Package weight(Lbs)	266.00 lb(US) (120.656 kg)
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	23.50 in (59.7 cm)
Package 1 width	24.02 in (61 cm)
Package 1 Length	28.19 in (71.6 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------