


## 1.50" X 3.00" T-slotted Profile - Six Open T-slots



Part No.	Series	Stock Length	Material	Alloy (or comparable)	Finish	Drop Lock	Moment of Inertia	Surface Area	Yield Strength	Modulus of Elasticity	Weight
1530		120", 242"			Clear Anodize						
1530-Black	<b>15</b>	120", 242"	Aluminum	6005A - T61	Black Anodize	2°	IX = 1.8042 <sup>in<sup>4</sup></sup> IY = 0.4824 <sup>in<sup>4</sup></sup>	2.077 in. <sup>2</sup>	35,000 psi	10,200,000 lb / in. <sup>2</sup>	0.2025 lb / in.
1530-Black-FB		per inch			Black Anodize						

### Standard Machining Services for 1.50" x 3.00"

Service No.	Series	Service Description	Reference Page
7020		Cut to Length	10-2
7050		Access Hole	10-5
7040	<b>15</b>	Anchor Counterbore	10-7
7045		Tap Profile End	10-3

Other machining services available in Section 10