



Main

Product or Component Type	Tap box
Range of Product	I-Line

Complementary

Mounting Mode	Plug-in
[Ue] rated operational voltage	277/480 V AC
Line Rated Current	225 A
Number of Phases	3 phase
Wiring configuration	4-wire (integral ground bus)
AWG gauge	AWG 6...AWG 2/0 1 ground 300 kcmil 1 phase and neutral
Material	Copper
Depth	7.76 in (197 mm)
Height	8.50 in (216 mm)
Width	16.38 in (416 mm)

Environment

Product Certifications	UL listed file E22182 CSA C22.2 No 27
Standards	UL 857

Ordering and shipping details

Category	20195-PBTB 225A TAP BOX
Discount Schedule	PE8
GTIN	785901087410
Nbr. of units in pkg.	1
Package weight(Lbs)	18.78 lb(US) (8.519 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	9.00 in (22.86 cm)
Package 1 width	12.20 in (30.988 cm)
Package 1 Length	18.30 in (46.482 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	24
Package 2 Weight	451.13 lb(US) (204.627 kg)

Package 2 Height	40.00 in (101.6 cm)
Package 2 width	36.00 in (91.44 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------