



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	SEE DETAIL	MATERIAL	"A" +/- .062	"B" +/- .062	INSIDE NOMINAL DIAMETER	MARKER ACROSS	TUBING COLOR	PKG. QTY.	SEE STYLE
H100X025H1T-2	B	GMUHS	1.00 [25.4]	3.50 [88.9]	1/8 in. [3.1 mm]	2	WHITE	1000	A
H200X025H1T-2	A		2.00 [50.8]			1	WHITE	500	
H100X025H2T-2	B		1.00 [25.4]			2	YELLOW	1000	
H200X025H2T-2	A		2.00 [50.8]			1	YELLOW	500	
H100X025H1T-2-B	B		1.00 [25.4]			B	2	WHITE	5000
H200X025H1T-2-B	A		2.00 [50.8]				1	WHITE	2500
H100X025H2T-2-B	B		1.00 [25.4]				2	YELLOW	5000
H200X025H2T-2-B	A		2.00 [50.8]				1	YELLOW	2500

NOTES:  
1. MILLIMETER ARE IN ( ).



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	1/22/14	RVU	SEWH	MSAD	UPDATE THE CURRENT PANDUIT LOGO.	GAECN01391
1	5/21/09	RVU		SCWE	ADD NEW PARTS: H100X025H1T-2-B, H200X025H1T-2-B, H100X025H2T-2-B, H200X025H2T-2-B. ADD NEW VIEW OF STYLE B. "B" +/- .062 WAS +/- .050, ETC.	5700
0	9/09/08	RVU		SCWE	DRAWING RELEASE.	5540

TITLE	
<b>H***X025H*T-2</b> <b>TWO-SIDED HEAT SHRINK LABEL</b> CUSTOMER DRAWING	
ITEM REVISION NAME	100472PE/03
DATASET FILE NAME	100472PE_DC_C10636/03C
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)	
.x ± .12 [3.04]	.xxx ± .020 [1.508]
.xx ± .062 [1.57]	ANGLES ±
THIRD ANGLE PROJECTION	
MATERIAL: <b>HEAT SHRINK TUBING, GMUHS31</b>	
DRAWING NUMBER: <b>C10636</b>	
DRAWN BY	DATE
RVU	9/09/08
CHK	SCALE
SCWE	NTS
SHT 1 OF 1	
SIZE A	

D10100DA/16