


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	WEIGHT lbs. / 100 Pcs. [ g / 100 Pcs. ]	CABLE TIE CROSS SECTION COMPATABILITY
ABM100-AV	0.33 [ 150 ]	MINIATURE INTERMEDIATE STANDARD




NOTES:

- SEE [www.panduit.com](http://www.panduit.com) FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.
- MOUNTS ARE SUPPLIED IN STRIPS OF TWO.
- MOUNT HAS A CONTINUOUS OPERATING TEMPERATURE OF 185°F (85°C).
- DIMENSIONS IN BRACKETS ARE METRIC [ mm ]
- NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.
- ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- HOLE FOR STANDARD S6 FLATHEAD SCREW.
- UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: ±0.030 [ 0.76 ]




TO APPLY MOUNTS:

- A** PRELIMINARY: CLEAN SURFACE WITH A CLEAN CLOTH AND ISOPROPYL ALCOHOL. ALLOW SURFACE TO AIR DRY.
- STEP 1: SCORE WITH UTILITY KNIFE BETWEEN MOUNT PAIRS TO BREAK WELD BACK.
- STEP 2: REMOVE MOUNT FROM PROTECTIVE LINER.
- STEP 3: PLACE IN DESIRED LOCATION.
- STEP 4: APPLY PRESSURE TO TOP SURFACE OF MOUNT.
- (IT IS RECOMMENDED THAT HIGH BOND ADHESIVE MOUNTS DWELL FOR 8 HOURS AFTER INSTALLATION, PRIOR TO LOADING)



SEE NOTE 7



**A** ADHESIVE BACKING:  
PRESSURE SENSITIVE FOAM TAPE  
0.025 [ 0.6mm ] THICK WITH PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 1.00 lbs. [ 454 g ] MAX. WEIGHT ON A CLEAN, DRY, SMOOTH, GREASE-FREE SURFACE.

PART NUMBER		ABM100-AV		
TITLE		VHB ADHESIVE BACKED MOUNTS		
ITEM REVISION NAME		CUSTOMER DRAWING		
DATASET FILE NAME		00202BBC/00		
		00202BBC_DC_ABM100-AV/00B		
MATERIAL		NYLON 6/6		
DRAWING NUMBER		00202BBC-DC		
THIRD ANGLE PROJECTION				
DRAWN BY	DATE	CHK	SCALE	SIZE
BDK	10.09.20	DAEI	NTS	A
REV	DATE	BY	CHK	APR
00	10.09.20	BDK	DAEI	MBVE
00B	03.15.21	BDK	MRJS	JADE

**A:** REVISED APPLICATION STEPS  
**B:** CHANGED DIMENSION ORIGIN  
**C:** CORRECTED SUPPORT WEIGHT; TAPE THICKNESS WAS 0.027 [ 0.69 ]  
**D:** TEMPERATURE WAS 120°F (49°C)  
**E:** MINIATURE WAS MEDIUM; REMOVED SG100M AND SG150I

RELEASED TO PRODUCTION

098736

GAECN081503

DESCRIPTION

ECN

SHEET 1 OF 1

A-SIZE CUSTOMER