THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. NOTES: 1. CONFORMS TO EIA--310-D SPECIFICATIONS FOR RACKS AND CABINETS. 2. THE BONDING CAGE NUT AND BONDING SCREW MUST BE USED TOGETHER TO ACHIEVE BONDING BETWEEN EQUIPMENT MOUNTING FLANGES AND CAGE NUT RAILS. DO NOT SUBSTITUTE THE BONDING CAGE NUT OR BONDING SCREW WITH ANY OTHERS. PART NUMBERS COMPONENT DESCRIPTION CNB4K CNBK QUANTITY BONDING CAGE NUT CAGE NUT RAIL THICKNESS TOLERANCE: 4 50 0.064 TO 0.105 in. [1.63mm TO .27 mm] GREEN SERRATIONS ON BONDING CAGE NUT PROVIDE BONDING-TO THE CAGE NUT RAIL GREEN BONDING SCREW, 1/2 in. [12.7 mm] LONG COMBO HEAD UTILIZES, #2 PHILLIPS OR 50 4 SERRATIONS UNDER HEAD OF SLOTTED SCREWDRIVER OR 5/16 in. BONDING SCREW PROVIDE OR 8mm SOCKET DRIVE BONDING TO THE EQUIPMENT FLANGE

							BONDING CAGE NUT KIT (CNB4K, CNBK) CUSTOMER DRAWING
							ITEM REVISION NAME N10966BD-C41747/04
							DATASET FILE NAME C41747/04.SLDDRW
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
							.X ± .XXX ± .XX ± ANGLES ±
04	3/13	JHNU	JHNU	RGB	REVISED TITLE BLOCK	N10966BD-C41747	THIRD ANGLE DRAWING NUMBER C41747_04
REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE SHEET 1 OF 1 SIZE   JHNU 4/08 JMAR NONE SHEET 1 OF 1 A