



80/20 T-slot Profiles

1.50" X 1.50" Ultra-Lite Smooth Surface T-slotted Profile - Four Open T-slots



Part No.	Series	Stock Length	Material	Alloy (or comparable)	Finish	Drop Lock	Moment of Inertia	Surface Area	Yield Strength	Modulus of Elasticity	Weight
1515-ULS		120", 242"			Clear Anodize						
1515-ULS-Black	15	120", 242"	Aluminum	6005A – T61	Black Anodize	2°	IX = 0.1765 ^{in.4} IY = 0.1765 ^{in.4}	2.290 in. ²	35,000 psi	10,200,000 lb / in. ²	0.0790 lb / in.
1515-ULS-Black-FB		per inch			Black Anodize						

1.50" X 1.50" Ultra-Lite T-slotted Profile - Four Open T-slots



Part No.	Series	Stock Length	Material	Alloy (or comparable)	Finish	Drop Lock	Moment of Inertia	Surface Area	Yield Strength	Modulus of Elasticity	Weight
1515-UL		120", 242"			Clear Anodize						
1515-UL-Black	15	120", 242"	Aluminum	6005A – T61	Black Anodize	2°	IX = 0.1772 ^{in.4} IY = 0.1772 ^{in.4}	0.787 in. ²	35,000 psi	10,200,000 lb / in. ²	0.0768 lb / in.
1515-UL-Black-FB		per inch			Black Anodize						

Standard Machining Services for 1.50" x 1.50"

Service No.	Series	Service Description	Reference Page
7010		Cut to Length	10-2
7050		Access Hole	10-5
7040	15	Anchor Counterbore	10-7
7060		Tap Profile End	10-3

Other machining services available in Section 10