


1.00" X 2.00" T-slotted Profile - Six Open T-slots



Part No.	Series	Stock Length	Material	Alloy (or comparable)	Finish	Drop Lock	Moment of Inertia	Surface Area	Yield Strength	Modulus of Elasticity	Weight
1020		120", 242"			Clear Anodize		$I_X = 0.3078^{in^4}$ $I_Y = 0.0833^{in^4}$	0.787 in. ²	35,000 psi	10,200,000 lb / in. ²	0.0768 lb / in.
1020-Black	10	120", 242"	Aluminum	6005A - T61	Black Anodize	2°					
1020-Black-FB		per inch			Black Anodize						

Standard Machining Services for 1.00" x 2.00"

Service No.	Series	Service Description	Reference Page
7000		Cut to Length	10-2
7051	10	Access Hole	10-5
7042		Anchor Counterbore	10-7
7046		Tap Profile End	10-3

Other machining services available in Section 10