


## Economy Lift-Off Hinge Left Hand with Short Pin



Part No.	Series	Max Load	A	B	C	D	E	F	G	H	J	K	L	M	Weight
2830	<b>10</b>	40 lb	1.062"	2.000"	1.000"	1.000"	.531"	.281"	.191"	.191"	.093"	.187"	.500"	1.000"	.045 lb
2832	<b>15</b>	70 lb	1.620"	3.000"	1.500"	1.500"	.812"	.328"	.250"	.250"	.120"	.250"	1.500"	1.500"	.134 lb
25-2830	<b>25</b>	18 kg	26.97mm	50.80mm	25.40mm	25.40mm	13.48mm	7.13mm	4.85mm	4.85mm	2.36mm	4.75mm	12.70mm	25.40mm	.0090 kg
40-2832	<b>40</b>	32 kg	41.15mm	76.20mm	38.10mm	41.02mm	20.62mm	8.30mm	6.35mm	6.35mm	3.05mm	6.35mm	19.05mm	50.80mm	.0607 kg

\*The gap distance between profiles for 10 series is .062", 15 series is .120", 25 series is 1.97mm, 40 series is 1.15mm.

### Material Specifications

Material	Alloy	Finish	Process
Aluminum	5052-H32 = Leaf 6061-T6 = Pin	Clear Anodize	Milled

### Suggested Hardware (Mount to T-Slot)

Part No.	Series	Qty.	Bolt	T-Nut
3386	<b>10</b>	4	1/4-20 x 3/8 FBHSCS	Economy
3319	<b>15</b>	4	5/16-18 x 1/2 FBHSCS	Economy
75-3404	<b>25</b>	4	M6 x 10mm BHSCS	Economy
75-3421	<b>40</b>	4	M8 x 12mm BHSCS	Economy

