


2.00" X 2.00" T-slotted Profile - Eight Open T-slots



Part No.	Series	Stock Length	Material	Alloy (or comparable)	Finish	Drop Lock	Moment of Inertia	Surface Area	Yield Strength	Modulus of Elasticity	Weight
2020		120", 242"			Clear Anodize						
2020-Black	10	120", 242"	Aluminum	6005A - T61	Black Anodize	2°	IX = 0.5509 ⁱⁿ⁴ IY = 0.5509 ⁱⁿ⁴	1.228 in. ²	35,000 psi	10,200,000 lb / in. ²	0.1198 lb / in.
2020-Black-FB		per inch			Black Anodize						

Standard Machining Services

Service No.	Series	Service Description	Reference Page
7012		Cut to Length	10-2
7051	10	Access Hole	10-5
7042		Anchor Counterbore	10-7
7064		Tap Profile End	10-3

Other machining services available in Section 10