

FL MGUARD 4302 - Router



1357840

<https://www.phoenixcontact.com/us/products/1357840>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Security appliance, 10/100/1000 Mbps, NAT, VPN, firewall



Product Description

Security appliance

Your advantages

- Central management tool
- Maximum security
- Maximum performance
- Integration of IT and OT security
- mGuard security technology

Commercial Data

Item number	1357840
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	DN29
Product Key	DNN311
GTIN	4063151685744
Weight per Piece (including packing)	468.7 g
Weight per Piece (excluding packing)	302 g
Customs tariff number	85176200
Country of origin	DE

Technical Data

Dimensions

Width	45 mm
Height	130 mm
Depth	133.8 mm

Material specifications

Color	gray
Housing material	Plastic

Interfaces

Ethernet

Connection method	RJ45
Transmission speed	10/100/1000 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
No. of channels	2 (RJ45 ports)

2x digital output, 2x digital input

Connection method	Push-in-/Spring-cage connection
Additional text	not electrically isolated

VPN - release button

Connection method	Push-in-/Spring-cage connection
-------------------	---------------------------------

System properties

Functionality

Basic functions	Security appliance with intelligent firewall and VPN for 250 tunnels, plastic housing, slot for SD memory card, extended temperature range, Gigabit wire speed
-----------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------

System requirements

Supported browsers	HTTPS support required
--------------------	------------------------

Product properties

Type	Stand-Alone
Product type	Security router for the DIN rail

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Security functions

1:1 Network Address Translation (NAT) in the VPN	Supported
Number of VPN tunnels	250

1357840

<https://www.phoenixcontact.com/us/products/1357840>

Authentication	X.509v3 certificates with RSA or PSK
Data integrity	MD5, SHA-1, SHA 256, SHA-512
Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Filtering	MAC and IP addresses, ports, protocols
Firewall data throughput	max. 940 Mbps (Router mode, default firewall rules, unidirectional throughput)
	max. 850 Mbps (Stealth mode, default firewall rules, unidirectional throughput)
Firewall rules	Configurable stateful inspection firewall with full scope of functions
Basic functions	Security appliance with intelligent firewall and VPN for 250 tunnels, plastic housing, slot for SD memory card, extended temperature range, Gigabit wire speed
Internet Protocol Security (IPsec) mode	ESP tunnel / ESP transport
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Network Time Protocol (NTP) client	Client/server
Remote Syslog Logging	On external server
Routing	Standard routing, NAT, 1:1-NAT, port forwarding
Protection against	IP spoofing, DoS and Syn Flood Protection
Encryption methods	DES, 3DES, AES-128, -192, -256
Virtual private network (VPN) throughput	max. 250 Mbps (Router mode, VPN unidirectional throughput)

Electrical properties

Local diagnostics	US1, US2 Supply voltage US1, US2 Green LED
	One LED per port Link active / Speed Green / green/yellow LED
Maximum power dissipation for nominal condition	typ. 2.88 W

Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	12 V DC ... 36 V DC
Power supply connection	via COMBICON, max. conductor cross section 1.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	1 A
Typical current consumption	120 mA (at U _S = 24 V DC)

Function

Signal contact control voltage	24 V DC (typical)
Signal contact control current	250 mA (short-circuit-proof)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

Standards and regulations

Free from substances that could impair the application of coating	Yes
-------------------------------------------------------------------	-----

Approvals

Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

Mounting

Mounting type	DIN rail mounting
Connection method	RJ45 jack, shielded

EMC data

Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) 6 kV contact discharge, 8 kV air discharge
	IEC 61000-6-2 IEC 61000-4-3 (immunity to radiated interference) 10 V/m (80 MHz ... 6000 MHz)
	IEC 61000-6-2 IEC 61000-4-4 (burst)
	IEC 61000-6-2 IEC 61000-4-5 (surge) power line: 1 kV (line/earth), 0.5 kV (line/line), 1 kV data line
	IEC 61000-6-2 IEC 61000-4-6 (immunity to conducted interference) 10 V (150 kHz ... 80 MHz)
Noise immunity	EN 61000-6-2:2005
Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 61000-6-4

Signaling

Status display	LEDs: US1, US2, FAIL, Link, and Activity
----------------	------------------------------------------

FL MGUARD 4302 - Router


1357840

<https://www.phoenixcontact.com/us/products/1357840>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1357840>

 **UL Listed**
Approval ID: E238705

 **cUL Listed**
Approval ID: E238705

FL MGUARD 4302 - Router

1357840

<https://www.phoenixcontact.com/us/products/1357840>



Classifications

ECLASS

ECLASS-11.0	19170406
ECLASS-12.0	19170406
ECLASS-13.0	19170406

ETIM

ETIM 8.0	EC001478
----------	----------

FL MGUARD 4302 - Router

1357840

<https://www.phoenixcontact.com/us/products/1357840>



Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
	4,4'-isopropylidenediphenol (BPA) 80-05-7

FL MGUARD 4302 - Router

1357840

<https://www.phoenixcontact.com/us/products/1357840>




Accessories

FL MGUARD DM UNLIMITED - Software

2981974

<https://www.phoenixcontact.com/us/products/2981974>



Central device management software for MGUARD devices for any number of devices in the field. For installation on a PC. No additional licenses required. Download trial version for up to 10 devices.

MGUARD SECURE VPN CLIENT LIC - License

2702579

<https://www.phoenixcontact.com/us/products/2702579>



License for mGuard Secure VPN Client v11.x

FL MGUARD 4302 - Router

1357840

<https://www.phoenixcontact.com/us/products/1357840>



SD FLASH 2GB - Program / configuration memory

2988162

<https://www.phoenixcontact.com/us/products/2988162>



Program and configuration memory, for extending the internal flash memory, pluggable, 2 GB.

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com