


1.50" X 3.00" Lite T-slotted Profile - Six Open T-slots



Part No.	Series	Stock Length	Material	Alloy (or comparable)	Finish	Drop Lock	Moment of Inertia	Surface Area	Yield Strength	Modulus of Elasticity	Weight
1530-Lite	15	120", 242"	Aluminum	6005A - T61	Clear Anodize	2"	IX = 1.3847 ⁱⁿ⁴ IY = 0.3935 ⁱⁿ⁴	1.722 in. ²	35,000 psi	10,200,000 lb / in. ²	0.1679 lb / in.
1530-Lite-Black		120", 242"			Black Anodize						
1530-Lite-Black-FB		per inch			Black Anodize						
1530-Lite-Yellow		120", 242"			Yellow Powder Coat						

Standard Machining Services for 1.50" x 3.00"

Service No.	Series	Service Description	Reference Page
7020	15	Cut to Length	10-2
7050		Access Hole	10-5
7040		Anchor Counterbore	10-7
7045		Tap Profile End	10-3

Other machining services available in Section 10