


| PART NUMBER | TONGUE MARKING | WIRE | WIRE STRIP LENGTH | STUD HOLE | A ± .01 | B ± .08 | D ± .01 | E ± .01 | G ± .01 | C ± .01 | T ± .03 | W ± .03 |
|-------------|----------------|------|-------------------|-----------|------------|------------|------------|------------|------------|------------|------------|------------|
| A8-10R-C | A8-10R | 8 | 9/16" | #10 | 1.26 | 0.50 | 0.25 | 0.18 | 0.25 | 0.56 | 0.05 | 0.43 |
| A8-14R-C | A8-14R | 8 | 9/16" | 1/4 | 1.32 | 0.50 | 0.25 | 0.18 | 0.25 | 0.62 | 0.05 | 0.43 |
| A8-56R-C | A8-56R | 8 | 9/16" | 5/16 | 1.45 | 0.50 | 0.25 | 0.18 | 0.33 | 0.75 | 0.04 | 0.51 |
| A8-38R-C | A8-38R | 8 | 9/16" | 3/8 | 1.54 | 0.50 | 0.25 | 0.18 | 0.36 | 0.84 | 0.04 | 0.54 |
| A6-10R-C | A6-10R | 6 | 9/16" | #10 | 1.47 | 0.50 | 0.31 | 0.23 | 0.32 | 0.76 | 0.07 | 0.47 |
| A6-14R-C | A6-14R | 6 | 9/16" | 1/4 | 1.47 | 0.50 | 0.31 | 0.23 | 0.32 | 0.76 | 0.07 | 0.54 |
| A6-56R-C | A6-56R | 6 | 9/16" | 5/16 | 1.47 | 0.50 | 0.31 | 0.23 | 0.32 | 0.76 | 0.07 | 0.54 |
| A6-38R-C | A6-38R | 6 | 9/16" | 3/8 | 1.47 | 0.50 | 0.31 | 0.23 | 0.32 | 0.76 | 0.07 | 0.54 |
| A4-14R-C | A4-14R | 4 | 5/8" | 1/4 | 1.51 | 0.61 | 0.35 | 0.27 | 0.25 | 0.62 | 0.06 | 0.55 |
| A4-56R-C | A4-56R | 4 | 5/8" | 5/16 | 1.63 | 0.61 | 0.35 | 0.27 | 0.32 | 0.74 | 0.06 | 0.61 |
| A4-38R-C | A4-38R | 4 | 5/8" | 3/8 | 1.73 | 0.61 | 0.35 | 0.27 | 0.36 | 0.84 | 0.06 | 0.61 |
| A2-14R-C | A2-14R | 2 | 3/4" | 1/4 | 1.84 | 0.74 | 0.42 | 0.31 | 0.36 | 0.74 | 0.10 | 0.60 |
| A2-56R-C | A2-56R | 2 | 3/4" | 5/16 | 1.89 | 0.74 | 0.42 | 0.31 | 0.36 | 0.80 | 0.10 | 0.66 |
| A2-38R-C | A2-38R | 2 | 3/4" | 3/8 | 1.93 | 0.74 | 0.42 | 0.31 | 0.36 | 0.83 | 0.10 | 0.66 |
| A2-12R-C | A2-12R | 2 | 3/4" | 1/2 | 2.16 | 0.74 | 0.42 | 0.31 | 0.47 | 1.07 | 0.08 | 0.75 |
| A1-14R-C | A1-14R | 1 | 13/16" | 1/4 | 1.90 | 0.77 | 0.47 | 0.36 | 0.36 | 0.74 | 0.11 | 0.70 |
| A1-56R-C | A1-56R | 1 | 13/16" | 5/16 | 1.96 | 0.77 | 0.47 | 0.36 | 0.36 | 0.80 | 0.11 | 0.70 |
| A1-38R-C | A1-38R | 1 | 13/16" | 3/8 | 1.99 | 0.77 | 0.47 | 0.36 | 0.36 | 0.83 | 0.11 | 0.70 |
| A1-12R-C | A1-12R | 1 | 13/16" | 1/2 | 2.23 | 0.77 | 0.47 | 0.36 | 0.47 | 1.07 | 0.09 | 0.79 |
| A1/0-56R-C | A1/0-56R | 1/0 | 13/16" | 5/16 | 2.01 | 0.80 | 0.52 | 0.39 | 0.36 | 0.80 | 0.12 | 0.76 |
| A1/0-38R-C | A1/0-38R | 1/0 | 13/16" | 3/8 | 2.05 | 0.80 | 0.52 | 0.39 | 0.37 | 0.84 | 0.12 | 0.76 |
| A1/0-12R-C | A1/0-12R | 1/0 | 13/16" | 1/2 | 2.28 | 0.80 | 0.52 | 0.39 | 0.47 | 1.07 | 0.12 | 0.82 |
| A2/0-56RC-C | A2/0-56RC | 2/0 | 15/16" | 5/16 | 2.16 | 0.88 | 0.58 | 0.45 | 0.35 | 0.80 | 0.13 | 0.85 |
| A2/0-38R-C | A2/0-38R | 2/0 | 15/16" | 3/8 | 2.26 | 0.88 | 0.58 | 0.45 | 0.45 | 0.90 | 0.13 | 0.85 |
| A2/0-12R-C | A2/0-12R | 2/0 | 15/16" | 1/2 | 2.46 | 0.88 | 0.58 | 0.45 | 0.51 | 1.10 | 0.13 | 0.85 |
| A3/0-56R-C | A3/0-56R | 3/0 | 13/16" | 5/16 | 2.27 | 0.80 | 0.62 | 0.51 | 0.48 | 1.02 | 0.10 | 0.91 |
| A3/0-38R-C | A3/0-38R | 3/0 | 13/16" | 3/8 | 2.27 | 0.80 | 0.62 | 0.51 | 0.48 | 1.02 | 0.10 | 0.91 |
| A3/0-12R-C | A3/0-12R | 3/0 | 13/16" | 1/2 | 2.32 | 0.80 | 0.62 | 0.51 | 0.48 | 1.07 | 0.10 | 0.91 |
| A4/0-56R-C | A4/0-56R | 4/0 | 15/16" | 5/16 | 2.57 | 0.91 | 0.69 | 0.56 | 0.52 | 1.14 | 0.12 | 1.02 |
| A4/0-38R-C | A4/0-38R | 4/0 | 15/16" | 3/8 | 2.57 | 0.91 | 0.69 | 0.56 | 0.52 | 1.14 | 0.12 | 1.02 |
| A4/0-12R-C | A4/0-12R | 4/0 | 15/16" | 1/2 | 2.57 | 0.91 | 0.69 | 0.56 | 0.52 | 1.14 | 0.12 | 1.02 |

NOTES:

- MATERIAL: HIGH CONDUCTIVITY SEAMLESS COPPER TUBE
- PLATING: ELECTRO-TIN
- WIRE TYPE: STRANDED COPPER; CLASS K



| REV | DATE | BY | CHK | APR | DESCRIPTION | |
|-----|---------|------|------|------|---|--|
| 09A | 4-25-23 | JHNU | JHNU | MRWA | B. ADDED cULUS LOGO A. CONVERTED DRAWING TO NX | |

| | | | |
|--------------------------------------|--------------------|-------------------------------|---------|
| PART NUMBER | SEE TABLE | | |
| TITLE | BATTERY CABLE LUGS | | |
| ITEM REVISION NAME 00159NBA/09 | | CUSTOMER DRAWING | |
| DATASET FILE NAME 00159NBA-DC/09A | | THIRD ANGLE PROJECTION | |
| | | DRAWING NUMBER 00159NBA-DC | |
| MATERIAL | | SEE NOTES | |
| DRAWN BY DAOS | | DATE 3-21-16 | CHK RGB |
| SCALE NONE | | SIZE B | |
| SHEET 1 OF 1 | | B | |