

A. System Overview

Metric Fork Terminal, Non-Insulated

B1. Cable Ties

Type PM-F

- Fork design provides for fast and easy installation, without the need to remove fastener
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Brazed seam protects terminal barrel from splitting during the crimp process
- Barrel of terminal internally beveled to provide quick and easy wire insertion
- Maximum recommended operating temperature 302°F (150°C)
- Rated up to 2000 V

B2. Cable Accessories


B3. Stainless Steel Ties



C1. Wiring Duct



C2. Surface Raceway



C3. Abrasion Protection

C4. Cable Management

| Part Number | Wire Range (mm²) | Stud Size | Figure Dimensions (mm) | | | Recommended Installation Tool | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-----------------|------------------|-----------|------------------------|------|-----|-------------------------------|----------------|----------------|
| | | | L | W | C | | | |
| PM1-3F-C | 0.5 – 1.5 | M3 | 16.0 | 5.8 | 5.6 | CT-1570, CT-2500 | 100 | 500 |
| PM1-4F-C | | M4 | 17.5 | 8.1 | 6.4 | | 100 | 500 |
| PM1-5F-C | | M5 | 18.0 | 8.8 | 6.6 | | 100 | 500 |
| PM2-3F-C | 1.0 – 2.5 | M3 | 16.0 | 5.8 | 5.6 | CT-1570, CT-2500 | 100 | 500 |
| PM2-4F-C | | M4 | 17.5 | 7.9 | 6.4 | | 100 | 500 |
| PM2-5F-C | | M5 | 18.0 | 8.6 | 6.9 | | 100 | 500 |
| PM6-5F-L | 4.0 – 6.0 | M5 | 19.4 | 9.5 | 7.1 | CT-1570, CT-2500 | 50 | 250 |
| PM6-6F-L | | M6 | 22.6 | 10.9 | 8.6 | | 50 | 250 |

For crimping tool information, see pages D1.84 and D1.88.

Plastic Box Terminal Kits

- Ideal for maintenance and construction wiring
- Positive latching case prevents accidental opening
- With the case top closed, parts remain in their compartments
- Case features a hanging tab for storage

D1. Terminals



KP-1075Y

D2. Power Connectors

D3. Grounding Connectors



KP-1165Y

| Part Number | Part Description | Std. Pkg. Qty. |
|-----------------|--|----------------|
| KP-1075Y | Terminal kit without crimping tool. Includes the following: (20) PV18-8R; PV18-6F; PV14-8F; PV14-10R; (10) PV10-8R; PV10-10R; DNF14-250; DNF18-250; BSV18X; BSV14X; BSV10X; (10) JN418-212. | 1 |
| KP-1000 | Empty plastic box, twelve terminal compartments and one tool compartment, measures 11" wide x 6 3/4" deep x 1 3/4" high. Positive latch prevents accidental opening. Once top is closed, terminals remain in their compartments. | 1 |
| KP-1165Y | Includes the following: (18) PV18-8R; PV14-10R; PV18-6F; PV14-8F; (10) PV10-8R; PV10-10R; BSV18X; BSV14X; BSV10X; DV18-250B; DV14-188B; (5) JN418-212; (1) CT-160 Tool; KP-1000 box. | 1 |
| KP-1166 | Includes the following: (18) P18-8R; P14-10R; P18-6F; P14-8F; (10) P10-8R; P10-10R; BS18; BS14; BS10; D18-250; D14-188; (5) JN218-216; (1) CT-160 tool; KP-1000 box. | 1 |

E1. Labeling Systems

E2. Labels

NEW! Fabric Terminal Kit

- Versatile fabric kit stores up to 5 standard packs of terminals
- Kit includes pocket for storage of an installation tool or cable ties
- Zipper closure prevents accidental opening
- Kit features a hanging tab for storage



Terminal parts sold separately



E4. Permanent Identification

E5. Lockout/Tagout & Safety Solutions

F. Index

| Part Number | Part Description | Std. Pkg. Qty. |
|----------------|--|----------------|
| KF-1005 | Empty fabric kit, 5 terminal compartments and one tool compartment, measures 5 1/2" wide x 2 1/2" deep x 11 1/2" high. | 1 |