

FEATURES

- Offer reliability
- Reduce the risk of dust and dirt entering the ball bearing mechanism
- Preserve the lubricant within the bearing
- Seals keep it running smoother, for longer

10mm Deep Groove Ball Bearing 19mm O.D

RS Stock No.: 261-2647



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

A range of RS PRO single row, deep groove ball bearings, offering versatility and overall high performance. RS PRO sealed ball bearings are fitted with two synthetic rubber seals to prevent dirt and other items entering the bearing. These ball bearings are primarily intended for use where the inner ring rotates.

General Specifications

Ball Bearing Type	Deep Groove
End Type	Sealed
Number of Rows	1
Static Load Rating	585N
Material	Steel
Race Type	Plain
Bore Type	Parallel
Application	Food and Beverage Industry, Pharmaceutical, Medical industry, Engines and Pumps, Medical Industry, Printing

Mechanical Specifications

Inside Diameter	10mm
Outside Diameter	19mm
Race Width	5mm
Dynamic Load Rating	1.38kN
Static Load	0.583kN
Mass	0.0050kg

