

ETHERLINE® 2 pair: CAT.5e 105C Plus; flexible

Industrial Ethernet cable for high temperature flexible applications

LAPP KABEL STUTTGART ETHERLINE® CAT.5e 105 Plus



ETHERLINE® 105C is designed to perform in high temperature applications. The 2 pair construction includes foil and braid shielding and a TPE-based jacket.

Construction

Conductors: bare copper wire

Insulation: polyethylene

Shielding: foil and copper braid

Jacket: TPE; green

Recommended applications

Flexible high temperature applications; installation in hollow shaft between gear units and pitch system; PLCs, sensors, and other network devices

Approvals



Application advantage

- Highly temperature resistant (105°C permanent, 120°C temporary)
- No need for additional protection against high temperatures
- Suitable for EtherCAT® & EtherNet/IP applications
- Conforms to PROFINET® standard
- Optimum EMC
- Suitable for PoE per IEEE 802.3at

Cable attributes

page 648

OIL OR-04

FLAME FR-00

MOTION FL-02

MECH. MP-05

Complete the installation



ÖLFLEX® CONNECT solution



ÖLFLEX® CONNECT CABLES
page 605

Technical data



Minimum bend radius:

- for stationary use: 10 x cable diameter
- for flexible use: 15 x cable diameter



Temperature range:

- for stationary use: -40°C to +105°C
(up to +120°C for temporary loads)
- for flexible use: -30°C to +105°C



Nominal voltage:

125V (not for power applications)



Characteristic impedance:

100Ω ± 15Ω



Color code:

white, yellow, blue, orange



Approvals:

RoHS

Part number	Construction	Stranding	Jacket material	Jacket color	Approvals	Fast connect	PoE	Nominal outer diameter		Approx. weight	SKINTOP® MS-SC
								in	mm	lbs/mft	PG thread
CAT.5e											
2170636	22 AWG/2pr	7 wire	TPE	green	PROFINET®	no	yes	0.244	6.2	36	53112210