

FEATURES

- 50 Ω impedance
- Operating frequency is 4GHz
- Gold-plated contacts ensure maximum efficiency
- Nickel plated body provides high load structure quality

RS PRO Family Name

RS Stock No.: 2469471



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These 50 Ω BNC right-angle RF coaxial crimping cable connectors have a nickel plated body, gold plated center contact, and are suitable for use with a wide range of RF coaxial cable types.

BNC connectors are suitable for a variety of applications including video signal transmission and test equipment.

General Specifications

Type of coaxial connector	BNC connector
Body Orientation	Right Angle
Body Plating	Nickel
Body Material	Copper
Termination Method	Crimp
Contact Material	Copper
Contact Plating	Gold
Gender	Male
Mounting Type	Cable Mount
Insulation Material	PTFE

Electrical Specifications

Temperature Range	-45° ~+165°
Characteristic Impedance	50Ω
Frequency Range	0~4GHz
Working Voltage	335V
Insulation Resistance	≥1000MΩ
Medium Pressure	750V(rms)
Working Life	500Cycles

Protection Category

--	--

Additional Information

EAN	
Custom Tariff Number	

Classification

eCl@ss (Version)	
UNSPSC (Version)	

Approvals

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
5463894	RS PRO	RF coaxial connector	50Ω impedance	Operating frequency is 4GHz	

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

