

# 190mm Plastic Backward Centrifugal Fan


## Characteristics:

- Material:**
Impeller: Plastic  
Rotor: Zinc Plating Steel  
Electronics housing: Die-cast aluminium
- Number of blades:** 7
- Direction of rotation:** Clockwise viewed toward rotor
- Insulation class:** "B"
- Installation position:** Any
- Degree of protection:** IP54
- Condensation drainage holes:** None
- Mode:** Continuous operation (S1)
- Mounting:** Maintenance-free ball bearings
- Technical features:** Controller input PWM or PWM/0-10V
- Cable exit:** Variable
- Protection class:** I (with customer connection of protective earth)
- Conformity with standards:** EN 60335-1
- Weight:** 1.4KG



## Performance:

Nominal data	Platform	Curve	Nominal voltage range	Frequency	Speed*	Max input power*	Max input current*	Operating ambient temp	Life time	PWM	PWM/0-10V
Type	Motor		VAC	Hz	rpm	W	A	°C	Hr		
ECO190CB235072112	OD72	A	230	50 / 60	3750	130	1.04	-20 to +60	40,000	●	
ECO190CB235072212											●



	n (rpm)	P1 (W)	I (A)	η (%)	P (Pa)	P (InH <sub>2</sub> O)	Q (CMH)	Q (CFM)
①	4010	135	1.03	—	0	0	889	524
②	3740	135	1.04	36.3	261	1.05	679	400
③	3750	136	1.04	49.7	493	1.98	494	291
④	3980	136	1.04	37.8	729	2.93	254	150
⑤	2980	59	0.51	—	0	0	654	385
⑥	2980	74	0.61	37.6	199	0.80	505	298
⑦	2980	71	0.59	46.7	327	1.31	365	215
⑧	2980	63	0.53	37.3	397	1.59	215	126
⑨	2490	37	0.34	—	0	0	543	320
⑩	2490	46	0.40	36.2	146	0.59	408	240
⑪	2490	43	0.38	43.2	224	0.90	301	177
⑫	2490	39	0.35	34.4	273	1.09	178	105
⑬	1990	22	0.21	—	0	0	431	254
⑭	1990	24	0.23	22.8	53	0.21	375	221
⑮	1990	25	0.24	38.4	122	0.49	287	169
⑯	1990	23	0.22	30.2	172	0.69	145	85

